

THM ET 28/28 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system M-Print® PRO under Windows optimise all labelling efforts.

- High-quality polyester labels in different colours
- Due to their flexible material and the thick adhesive layer, the THM GEW can be used on angled or round objects such as cables or hoses
- Roll-packaged THM ET S7 can be used to label the Simatic 200S, S7-300 and S7-400 modules from Siemens
- Labels are automatically positioned in the printer for perfectly centred prints on each label.
- Labelling with the THM MultiMark or THM MultiMark Plus thermal transfer printers

General ordering data

Version	Conductor and cable markers, 28 x 28 mm, white
Order No.	2539410000
Type	THM ET 28/28 WS
GTIN (EAN)	4050118570182
Qty.	1500 items

THM ET 28/28 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.35 mm	Depth (inches)	0.0138 inch
Height	28 mm	Height (inches)	1.1024 inch
Width	28 mm	Width (inches)	1.1024 inch
Net weight	0.39 g		

Temperatures

Operating temperature range	-50...100 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Version	Self-adhesive	Width	28 mm
UL 94 flammability rating	HB	Operating temperature range, max.	100 °C
Operating temperature range, min.	-50 °C	Colour	white
Halogen	No	Basic material	Polypropylene
Printed characters	without	Operating temperature range	-50...100 °C

Conductor and cable markers

Halogen	No
---------	----

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

