


A2T 4 PE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

To feed through power, signal, and data is the classical requirement in electrical engineering and panel building. The insulating material, the connection system and the design of the terminal blocks are the differentiating features. A feed-through terminal block is suitable for joining and/or connecting one or more conductors. They could have one or more connection levels that are on the same potential or insulated against one another.

General ordering data

| | |
|------------|---|
| Version | PE terminal, PUSH IN, 4 mm ² , 800 V, Green/yellow |
| Order No. | 2539990000 |
| Type | A2T 4 PE |
| GTIN (EAN) | 4050118551846 |
| Qty. | 50 items |

A2T 4 PE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|---------------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E60693 |
| Certificate No. (cURusEX) | E184763 |

Dimensions and weights

| | | | |
|--------------------------|-------------|----------------|-------------|
| Depth | 53.5 mm | Depth (inches) | 2.1063 inch |
| Depth including DIN rail | 54.5 mm | Height | 100 mm |
| Height (inches) | 3.937 inch | Width | 6.1 mm |
| Width (inches) | 0.2402 inch | Net weight | 24.49 g |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|---------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -5 °C...40 °C |
| Continuous operating temp., min. | -60 °C | Continuous operating temp., max. | 130 °C |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|--------------------------------|--------|---------------------------|--------------|
| Basic material | Wemid | Colour | Green/yellow |
| Colour of operational elements | orange | UL 94 flammability rating | V-0 |

Rating data IECEx/ATEX

| | | | |
|--------------------------------|-------------------|---------------------------------|-------------------|
| Certificate No. (ATEX) | TUEV16ATEX7909U | Certificate No. (IECEX) | IECEXTUR16.0036U |
| Wire cross section max. (ATEX) | 4 mm ² | Wire cross section max. (IECEX) | 4 mm ² |

System specifications

| | | | |
|-------------------------------|-------|-------------------------------------|-----|
| End cover plate required | Yes | Number of potentials | 1 |
| Number of levels | 2 | Number of clamping points per level | 2 |
| Number of potentials per tier | 1 | PE connection | Yes |
| Mounting rail | TS 35 | N-function | No |
| PE function | Yes | PEN function | No |

Additional technical data

| | | | |
|---------------------|------|------------------|---------|
| With snap-in pegs | No | Open sides | right |
| Snap-on | No | Type of fixing | Snap-on |
| Installation advice | Rail | Type of mounting | TS 35 |

A2T 4 PE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Conductors for clamping (additional connection)

Connection type, additional connection PUSH IN

Conductors for clamping (rated connection)

| | | | |
|---|--|---------------------|---------------------|
| Gauge to IEC 60947-1 | A4 | | |
| Wire connection cross section AWG, max. | AWG 12 | | |
| Connection direction | top | | |
| Stripping length | 12 mm | | |
| Type of connection | PUSH IN | | |
| Number of connections | 4 | | |
| Clamping range, max. | 6 mm ² | | |
| Clamping range, min. | 0.14 mm ² | | |
| Blade size | 0.6 x 3.5 mm | | |
| Wire connection cross section AWG, min. | AWG 26 | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 4 mm ² | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.14 mm ² | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 6 mm ² | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.14 mm ² | | |
| Wire connection cross section, finely stranded, max. | 6 mm ² | | |
| Wire connection cross section, finely stranded, min. | 0.14 mm ² | | |
| Connection cross-section, stranded, max. | 6 mm ² | | |
| Connection cross-section, stranded, min. | 0.14 mm ² | | |
| Twin wire-end ferrules, max. | 1.5 mm ² | | |
| Twin wire-end ferrules, min. | 0.5 mm ² | | |
| Wire connection cross-section, solid core, max. | 4 mm ² | | |
| Wire connection cross-section, solid core, min. | 0.14 mm ² | | |
| Tube length for wire-end ferrule with plastic collar DIN 46228/4 | Tube length | min. | 6 mm |
| | | max. | 12 mm |
| | Cross-section for conductor connection | min. | 0.5 mm ² |
| | | max. | 1 mm ² |
| | Tube length | min. | 8 mm |
| | | max. | 12 mm |
| Cross-section for conductor connection | min. | 1.5 mm ² | |
| | max. | 2.5 mm ² | |
| Tube length for twin wire-end ferrule | Tube length | min. | 8 mm |
| | | max. | 12 mm |
| | Cross-section for conductor connection | min. | 0.5 mm ² |
| | | max. | 1.5 mm ² |
| | Tube length | min. | 10 mm |
| | | max. | 12 mm |
| Cross-section for conductor connection | nominal | 4 mm ² | |
| | | | |
| Tube length for wire-end ferrule without plastic collar DIN 46228/1 | Tube length | min. | 6 mm |
| | | max. | 10 mm |
| | Cross-section for conductor connection | min. | 0.5 mm ² |
| | | max. | 1.5 mm ² |

A2T 4 PE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

| | | |
|--|------|---------------------|
| Cross-section for conductor connection | min. | 0.5 mm ² |
| | max. | 1 mm ² |
| Tube length | min. | 7 mm |
| | max. | 12 mm |
| Cross-section for conductor connection | min. | 1.5 mm ² |
| | max. | 2.5 mm ² |
| Tube length | min. | 9 mm |
| | max. | 15 mm |
| Cross-section for conductor connection | min. | 4 mm ² |
| | max. | 6 mm ² |

General

| | | | |
|---|--------|---------------------|---------------|
| Wire connection cross section AWG, max. | AWG 12 | Installation advice | Rail |
| Wire connection cross section AWG, min. | AWG 26 | Standards | IEC 60947-7-2 |
| Mounting rail | TS 35 | | |

Rating data

| | | | |
|--|-------------------|--|--------|
| Rated cross-section | 4 mm ² | Rated voltage | 800 V |
| Rated voltage to adjoining terminal | 800 V | Rated DC voltage | 800 V |
| Standards | IEC 60947-7-2 | Volume resistance according to IEC 60947-7-x | 1 mΩ |
| Rated impulse withstand voltage to adjacent terminal | 8 kV | Power loss in accordance with IEC 60947-7-x | 0.00 W |
| Surge voltage category | III | Pollution severity | 3 |

UL rating data

| | | | |
|---|--------|--|--------|
| Conductor size Factory wiring max. (cURus) | 10 AWG | Voltage size B (cURus) | 600 V |
| Voltage size D (cURus) | 600 V | Certificate No. (cURus) | E60693 |
| Conductor size Field wiring min. (cURus) 26 AWG | | Conductor size Factory wiring min. (cURus) | 26 AWG |
| Voltage size C (cURus) | 600 V | Conductor size Field wiring max. (cURus) | 10 AWG |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000901 | ETIM 9.0 | EC000901 |
| ETIM 10.0 | EC000901 | ECLASS 14.0 | 27-25-01-04 |
| ECLASS 15.0 | 27-25-01-04 | | |

Drawings

