

SAI-M12L-KSC-0.75FE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

General ordering data

Version	Crimp contact
Order No.	2530970000
Type	SAI-M12L-KSC-0.75FE
GTIN (EAN)	4050118541083
Qty.	50 items

SAI-M12L-KSC-0.75FE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Length	24.8 mm	Length (inches)	0.9764 inch
Net weight	0.6 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4

Technical data customisable plug-in connectors

Contact surface	Gold-plated	Type of connection	Crimp connection
Contact material	Cu	Nominal voltage	63 V
Nominal current	16 A	Plugging cycles	500
Pollution severity	3	Gender of contact	Male

General Info

Connection 1	M12 Contact	Connection 2	Crimp
Contact material	Cu	Contact surface	Gold-plated
Wire connection cross section, finely stranded, min.	0.75 mm ²	Wire connection cross section, finely stranded, max.	0.75 mm ²
Wire cross-section, solid, min.	0.75 mm ²	Wire cross-section, solid, max.	0.75 mm ²
Plugging cycles	500		

Standards

Connector standard	IEC 61076-2-111
--------------------	-----------------

Classifications

ETIM 8.0	EC000796	ETIM 9.0	EC000796
ETIM 10.0	EC000796	ECLASS 14.0	27-44-02-92
ECLASS 15.0	27-44-02-92		

Dimensioned drawing



Pin