


## APGTB 4 FT 4C/2

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Product image



Some applications demand for a pluggable, modular solution to be more flexible or to facilitate the installation. Where complete functional units have to be prefabricated or replaced, modular and flexible connection systems are required. Our pluggable terminal blocks can be quickly assembled and are completely factory tested.

### General ordering data

|            |   |
|------------|---|
| Version    | Plug-in modular terminals, PUSH IN, 4 mm <sup>2</sup> , 800 V, 32 A, dark beige |
| Order No.  | <a href="#">2540090000</a>  |
| Type       | APGTB 4 FT 4C/2   |
| GTIN (EAN) | 4050118551945   |
| Qty.       | 50 items  |

## APGTB 4 FT 4C/2

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E60693

## Dimensions and weights

|                          |             |                |             |
|--------------------------|-------------|----------------|-------------|
| Depth                    | 39.5 mm     | Depth (inches) | 1.5551 inch |
| Depth including DIN rail | 40.5 mm     | Height         | 98 mm       |
| Height (inches)          | 3.8583 inch | Width          | 6.1 mm      |
| Width (inches)           | 0.2402 inch | Net weight     | 15.04 g     |

## Temperatures

|                                  |                |                                  |               |
|----------------------------------|----------------|----------------------------------|---------------|
| Storage temperature              | -25 °C...55 °C | Ambient temperature              | -5 °C...40 °C |
| Continuous operating temp., min. | -60 °C         | Continuous operating temp., max. | 130 °C        |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Material data

|                                |        |                           |            |
|--------------------------------|--------|---------------------------|------------|
| Basic material                 | Wemid  | Colour                    | dark beige |
| Colour of operational elements | orange | UL 94 flammability rating | V-0        |

## System specifications

|                               |     |                                     |       |
|-------------------------------|-----|-------------------------------------|-------|
| End cover plate required      | Yes | Number of potentials                | 1     |
| Number of levels              | 1   | Number of clamping points per level | 4     |
| Number of potentials per tier | 1   | Levels cross-connected internally   | No    |
| PE connection                 | No  | Mounting rail                       | TS 35 |
| N-function                    | No  | PE function                         | No    |
| PEN function                  | No  |                                     |       |

## Additional technical data

|                     |       |                          |         |
|---------------------|-------|--------------------------|---------|
| With snap-in pegs   | No    | Open sides               | right   |
| Snap-on             | No    | Type of fixing           | Snap-on |
| Installation advice | Rail  | Explosion-tested version | No      |
| Type of mounting    | TS 35 |                          |         |

## CSA rating data

|                               |        |                       |                 |
|-------------------------------|--------|-----------------------|-----------------|
| Wire cross section max. (CSA) | 10 AWG | Voltage size C (CSA)  | 600 V           |
| Current size C (CSA)          | 30 A   | Certificate No. (CSA) | 200039-70089609 |
| Voltage size B (CSA)          | 600 V  | Current size B (CSA)  | 30 A            |
| Voltage size D (CSA)          | 600 V  | Current size D (CSA)  | 5 A             |
| Wire cross section min. (CSA) | 26 AWG |                       |                 |

## APGTB 4 FT 4C/2

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Conductors for clamping (additional connection)

Connection type, additional connection pluggable

### Conductors for clamping (rated connection)

|   |  |                   |                     |
|---|--|-------------------|---------------------|
| Gauge to IEC 60947-1  | A4                                     |                   |                     |
| Wire connection cross section AWG, max.   | AWG 12                                 |                   |                     |
| Connection direction  | top                                    |                   |                     |
| Stripping length  | 12 mm                                  |                   |                     |
| Type of connection 2  | Plug-in connection                     |                   |                     |
| Type of connection  | PUSH IN                                |                   |                     |
| Number of connections   | 2                                      |                   |                     |
| Clamping range, max.  | 6 mm <sup>2</sup>                      |                   |                     |
| Clamping range, min.  | 0.14 mm <sup>2</sup>                   |                   |                     |
| Blade size  | 0.6 x 3.5 mm                           |                   |                     |
| Wire connection cross section AWG, min.   | AWG 26                                 |                   |                     |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 4 mm <sup>2</sup>                      |                   |                     |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.14 mm <sup>2</sup>                   |                   |                     |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 6 mm <sup>2</sup>                      |                   |                     |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.14 mm <sup>2</sup>                   |                   |                     |
| Wire connection cross section, finely stranded, max.                                    | 6 mm <sup>2</sup>                      |                   |                     |
| Wire connection cross section, finely stranded, min.                                    | 0.14 mm <sup>2</sup>                   |                   |                     |
| Connection cross-section, stranded, max.  | 6 mm <sup>2</sup>                      |                   |                     |
| Connection cross-section, stranded, min.  | 0.14 mm <sup>2</sup>                   |                   |                     |
| Twin wire-end ferrules, max.  | 1.5 mm <sup>2</sup>                    |                   |                     |
| Twin wire-end ferrules, min.  | 0.5 mm <sup>2</sup>                    |                   |                     |
| Wire connection cross-section, solid core, max.   | 4 mm <sup>2</sup>                      |                   |                     |
| Wire connection cross-section, solid core, min.   | 0.14 mm <sup>2</sup>                   |                   |                     |
| Tube length for wire-end ferrule with plastic collar DIN 46228/4                        | Tube length                            | min.              | 6 mm                |
|   |  | max.              | 12 mm               |
|   | Cross-section for conductor connection | min.              | 0.5 mm <sup>2</sup> |
|   |  | max.              | 1 mm <sup>2</sup>   |
|   | Tube length                            | min.              | 8 mm                |
|   |  | max.              | 12 mm               |
|   | Cross-section for conductor connection | min.              | 1.5 mm <sup>2</sup> |
|   |  | max.              | 2.5 mm <sup>2</sup> |
| Tube length   | min.                                   | 10 mm             |                     |
|   | max.                                   | 12 mm             |                     |
| Cross-section for conductor connection  | nominal                                | 4 mm <sup>2</sup> |                     |
|   |  |                   |                     |
| Tube length for twin wire-end ferrule   | Tube length                            | min.              | 8 mm                |
|   |  | max.              | 12 mm               |
|   | Cross-section for conductor connection | min.              | 0.5 mm <sup>2</sup> |
|   |  | max.              | 1.5 mm <sup>2</sup> |

## APGTB 4 FT 4C/2

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

|   |  |      |                     |
|---|--|------|---------------------|
| Tube length for wire-end ferrule without plastic collar DIN 46228/1 | Tube length                            | min. | 6 mm                |
|   |  | max. | 10 mm               |
|   | Cross-section for conductor connection | min. | 0.5 mm <sup>2</sup> |
|   |  | max. | 1 mm <sup>2</sup>   |
|   | Tube length                            | min. | 7 mm                |
|   |  | max. | 12 mm               |
|   | Cross-section for conductor connection | min. | 1.5 mm <sup>2</sup> |
|   |  | max. | 2.5 mm <sup>2</sup> |
|   | Tube length                            | min. | 9 mm                |
|   |  | max. | 15 mm               |
|   | Cross-section for conductor connection | min. | 4 mm <sup>2</sup>   |
|   |  | max. | 6 mm <sup>2</sup>   |

### General

|   |        |                     |       |
|---|--------|---------------------|-------|
| Wire connection cross section AWG, max. | AWG 12 | Installation advice | Rail  |
| Wire connection cross section AWG, min. | AWG 26 | Mounting rail       | TS 35 |

### Rating data

|                                 |                   |  |        |
|---------------------------------|-------------------|--|--------|
| Rated cross-section             | 4 mm <sup>2</sup> | Rated voltage                                | 800 V  |
| Rated DC voltage                | 800 V             | Nominal current                              | 32 A   |
| Current at maximum wires        | 32 A              | Volume resistance according to IEC 60947-7-x | 1 mΩ   |
| Rated impulse withstand voltage | 8 kV              | Power loss in accordance with IEC 60947-7-x  | 1.02 W |
| Surge voltage category          | III               | Pollution severity                           | 3      |

### UL rating data

|  |        |  |        |
|--|--------|--|--------|
| Conductor size Factory wiring max. (cURus) | 10 AWG | Voltage size B (cURus)                     | 600 V  |
| Voltage size D (cURus)                     | 600 V  | Certificate No. (cURus)                    | E60693 |
| Conductor size Field wiring min. (cURus)   | 26 AWG | Conductor size Factory wiring min. (cURus) | 26 AWG |
| Current size B (cURus)                     | 30 A   | Voltage size C (cURus)                     | 600 V  |
| Current size C (cURus)                     | 30 A   | Current size D (cURus)                     | 5 A    |
| Conductor size Field wiring max. (cURus)   | 10 AWG |  |        |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000897    | ETIM 9.0    | EC000897    |
| ETIM 10.0   | EC000897    | ECLASS 14.0 | 27-25-01-17 |
| ECLASS 15.0 | 27-25-01-17 |             |             |

**Drawings**

