

WQB 4 WTL 6/4 FF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image**Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

General ordering data

Version	Cross-connector (terminal), when screwed in, orange, 41 A, Number of poles: 4, Pitch in mm (P): 11.10, Insulated: Yes, Width: 40.4 mm
Order No.	2550750000
Type	WQB 4 WTL 6/4 FF
GTIN (EAN)	4050118560619
Qty.	10 items

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	5 mm	Depth (inches)	0.1968 inch
Height	29.32 mm	Height (inches)	1.1543 inch
Width	40.4 mm	Width (inches)	1.5905 inch
Net weight	4.2 g		

Temperatures

Storage temperature -25 °C...55 °C Ambient temperature -5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Material data

Basic material Wemid Colour orange

System specifications

Version Cross-connector

Additional technical data

Type of fixing when screwed in Installation advice Direct mounting
 Explosion-tested version No Type of mounting when screwed in

Dimensions

Pitch in mm (P) 11.10 mm

General

Number of poles 4 Installation advice Direct mounting

Rating data

Nominal current 41 A

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		