


**WQB 5 WTL 6/4 FF**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, orange, 41 A, Number of poles: 5, Pitch in mm (P): 11.10, Insulated: Yes, Width: 51.5 mm
Order No.	<a href="#">2550760000</a>
Type	WQB 5 WTL 6/4 FF
GTIN (EAN)	4050118560626
Qty.	10 items

## WQB 5 WTL 6/4 FF

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	5 mm	Depth (inches)	0.1968 inch
Height	29.32 mm	Height (inches)	1.1543 inch
Width	51.5 mm	Width (inches)	2.0276 inch
Net weight	9.77 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	Wemid	Colour	orange
----------------	-------	--------	--------

## System specifications

Version	Cross-connector
---------	-----------------

## Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No	Type of mounting	when screwed in

## Dimensions

Pitch in mm (P)	11.10 mm
-----------------	----------

## General

Number of poles	5	Installation advice	Direct mounting
-----------------	---	---------------------	-----------------

## Rating data

Nominal current	41 A
-----------------	------

## Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		