



**B2CF 3.50/38/180 SN BK BX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Product image**

Two-row female plug with PUSH IN spring connection

- Simply insert the prepared wire - and you're done
- Intuitive to use because
- the wire-entry area and handling area are clearly separated
- Integrated push-buttons for opening the terminal point
- High component density because of low heights
- Optional: locking and releasing require no tools when using Weidmüller's release latch (LR) or release lever (LH)

**General ordering data**

Version	PCB plug-in connector, female plug, 3.50 mm, Number of poles: 38, 180°, PUSH IN with push button, Clamping range, max. : 1.5 mm <sup>2</sup> , Box
Order No.	<a href="#">2558460000</a>
Type	B2CF 3.50/38/180 SN BK BX
GTIN (EAN)	4050118681208
Qty.	24 items
Product data	IEC: 320 V / 13.4 A / 0.14 - 1.5 mm <sup>2</sup> UL: 300 V / 9.5 A / AWG 30 - AWG 16
Packaging	Box

**B2CF 3.50/38/180 SN BK BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergsstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Approvals**

RoHS	Conform
------	---------

**Dimensions and weights**

Depth	25.25 mm	Depth (inches)	0.9941 inch
Height	15.2 mm	Height (inches)	0.5984 inch
Width	66.5 mm	Width (inches)	2.6181 inch
Net weight	25.61 g		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**System Parameters**

Product family	OMNIMATE Signal - series B2C/S2C 3.50 - 2-row	Type of connection	Field connection
Wire connection method	PUSH IN with push button	Pitch in mm (P)	3.50 mm
Pitch in inches (P)	0.138 "	Conductor outlet direction	180°
Number of poles	38	L1 in mm	63.00 mm
L1 in inches	2.484 "	Number of rows	1
Pin series quantity	2	Rated cross-section	15 mm <sup>2</sup>
Touch-safe protection acc. to DIN VDE 57 106	Safe from finger touch	Touch-safe protection acc. to DIN VDE 0470	IP20 plugged
Protection degree	IP20, when fully mounted	Can be coded	Yes
Stripping length	10 mm	Screwdriver blade	0.4 x 2.5
Screwdriver blade standard	DIN 5264	Plugging cycles	25
Plugging force/pole, max.	3.5 N	Pulling force/pole, max.	3.5 N

**Material data**

Insulating material	PA 66 GF 30	Colour	black
Colour chart (similar)	RAL 9011	Insulating material group	II
Comparative Tracking Index (CTI)	≥ 600	Insulation resistance	≥ 108 Ω
Moisture Level (MSL)		UL 94 flammability rating	V-0
Contact material	Copper alloy	Contact surface	tinned
Layer structure of plug contact	2...5 µm Sn hot-dip tinned	Storage temperature, min.	-40 °C
Storage temperature, max.	70 °C	Operating temperature, min.	-50 °C
Operating temperature, max.	120 °C	Temperature range, installation, min.	-40 °C
Temperature range, installation, max.	120 °C		

**Conductors suitable for connection**

Clamping range, min.	0.14 mm <sup>2</sup>
Clamping range, max.	1.5 mm <sup>2</sup>
Wire connection cross section AWG, min.	AWG 30
Wire connection cross section AWG, max.	AWG 16
Solid, min. H05(07) V-U	0.14 mm <sup>2</sup>
Solid, max. H05(07) V-U	1.5 mm <sup>2</sup>
Flexible, min. H05(07) V-K	0.14 mm <sup>2</sup>
Flexible, max. H05(07) V-K	1.5 mm <sup>2</sup>
w. plastic collar ferrule, DIN 46228 pt 4, 0.14 mm <sup>2</sup> min.	

## B2CF 3.50/38/180 SN BK BX

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

w. plastic collar ferrule, DIN 46228 pt 4, 1 mm<sup>2</sup>

max.

w. wire end ferrule, DIN 46228 pt 1, 0.14 mm<sup>2</sup>

min.

w. wire end ferrule, DIN 46228 pt 1, 1.5 mm<sup>2</sup>

max.

Clampable conductor

Cross-section for conductor connection	Type	fine-wired
	nominal	0.14 mm <sup>2</sup>
	wire end ferrule	Stripping length nominal 10 mm Recommended wire-end ferrule <a href="#">H0.14/12 GR SV</a>
	Cross-section for conductor connection	Type fine-wired
	nominal	0.25 mm <sup>2</sup>
	wire end ferrule	Stripping length nominal 10 mm Recommended wire-end ferrule <a href="#">H0.25/12 HBL SV</a>
	Cross-section for conductor connection	Type fine-wired
	nominal	0.34 mm <sup>2</sup>
	wire end ferrule	Stripping length nominal 10 mm Recommended wire-end ferrule <a href="#">H0.34/12 TK SV</a>
	Cross-section for conductor connection	Type fine-wired
wire end ferrule	nominal	0.5 mm <sup>2</sup>
	Cross-section for conductor connection	Stripping length nominal 12 mm Recommended wire-end ferrule
	nominal	0.75 mm <sup>2</sup>
	wire end ferrule	Stripping length nominal 12 mm Recommended wire-end ferrule <a href="#">H0.75/16 W SV</a>
	Cross-section for conductor connection	Stripping length nominal 10 mm Recommended wire-end ferrule <a href="#">H0.75/10</a>
	nominal	1
	wire end ferrule	Stripping length nominal 12 mm Recommended wire-end ferrule <a href="#">H1.0/16 GE SV</a>
	Cross-section for conductor connection	Stripping length nominal 10 mm Recommended wire-end ferrule <a href="#">H1.0/10</a>
	nominal	1.5 mm <sup>2</sup>
	wire end ferrule	Stripping length nominal 10 mm Recommended wire-end ferrule <a href="#">H1.5/10</a>

Reference text

The outside diameter of the plastic collar should not be larger than the pitch (P). Length of ferrules is to be chosen depending on the product and the rated voltage.

## Rated data acc. to IEC

tested acc. to standard	IEC 60664-1, IEC 61984	Rated current, min. number of poles (Tu=20°C)	13.4 A
Rated current, max. number of poles (Tu=20°C)	10 A	Rated current, min. number of poles (Tu=40°C)	12 A
Rated current, max. number of poles (Tu=40°C)	9 A	Rated voltage for surge voltage class / pollution degree II/2	320 V
Rated voltage for surge voltage class / pollution degree III/2	160 V	Rated voltage for surge voltage class / pollution degree III/3	160 V

**B2CF 3.50/38/180 SN BK BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergsstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

Rated impulse voltage for surge voltage 2.5 kV  
 class/ pollution degree II/2

Rated impulse voltage for surge voltage 2.5 kV  
 class/ contamination degree III/3

Rated impulse voltage for surge voltage 2.5 kV  
 class/ pollution degree III/2

Short-time withstand current resistance 3 x 1s with 80 A

**Rated data acc. to CSA**

Rated voltage (Use group B / CSA) 300 V  
 Rated voltage (Use group D / CSA) 300 V  
 Rated current (Use group C / CSA) 9.5 A  
 Wire cross-section, AWG, min. AWG 30

Rated voltage (Use group C / CSA) 50 V  
 Rated current (Use group B / CSA) 9.5 A  
 Rated current (Use group D / CSA) 9.5 A  
 Wire cross-section, AWG, max. AWG 16

**Rated data acc. to UL 1059**

Rated voltage (Use group B / UL 1059) 300 V  
 Rated voltage (Use group D / UL 1059) 300 V  
 Rated current (Use group C / UL 1059) 9.5 A  
 Wire cross-section, AWG, min. AWG 30

Rated voltage (Use group C / UL 1059) 50 V  
 Rated current (Use group B / UL 1059) 9.5 A  
 Rated current (Use group D / UL 1059) 9.5 A  
 Wire cross-section, AWG, max. AWG 16

**Packing**

Packaging Box  
 VPE width 130.00 mm

VPE length 338.00 mm  
 VPE height 33.00 mm

**Type tests**

Test: Durability of markings	Standard	IEC 61984 section 6.2 and 7.3.2 / 10.11 taking pattern from IEC 60068-2-70 / 12.95
	Test	mark of origin, type identification, pitch, type of material, date clock, approval marking UL, approval marking cULus
	Evaluation	available
	Test	durability
	Evaluation	passed
	Standard	IEC 61984 section 6.3 and 6.9.1 / 10.11, IEC 60512-13-5 / 02.06
Test: Misengagement (Non-interchangeability)	Test	180° turned without coding elements
	Evaluation	passed
	Test	180° turned with coding elements
	Evaluation	passed
	Test	visual examination
	Evaluation	passed
Test: Clampable cross section	Standard	IEC 60999-1 section 7 and 9.1 / 11.99, IEC 60947-1 section 8.2.4.5.1 / 03.11
	Conductor type	Type of conductor solid 0.14 mm <sup>2</sup> and conductor cross-section
		Type of conductor stranded 0.14 mm <sup>2</sup> and conductor cross-section
		Type of conductor solid 1.5 mm <sup>2</sup> and conductor cross-section
		Type of conductor stranded 1.5 mm <sup>2</sup> and conductor cross-section
		Type of conductor AWG 26/1 and conductor cross-section

## B2CF 3.50/38/180 SN BK BX

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

Test for damage to and accidental loosening of conductors		Type of conductor and conductor cross-section	AWG 26/19
		Type of conductor and conductor cross-section	AWG 16/1
		Type of conductor and conductor cross-section	AWG 16/19
		Evaluation	passed
		Standard	IEC 60999-1 section 9.4 / 11.99
		Requirement	0.2 kg
		Conductor type	Type of conductor and conductor cross-section
			AWG 26/1
			AWG 26/19
		Evaluation	passed
Pull-out test		Requirement	0.3 kg
		Conductor type	Type of conductor and conductor cross-section
			H05V-U0.75
			H05V-K0.75
		Evaluation	passed
		Requirement	0.4 kg
		Conductor type	Type of conductor and conductor cross-section
			H07V-U1.5
			H07V-K1.5
			AWG 16/1
			AWG 16/19
		Evaluation	passed
		Standard	IEC 60999-1 section 9.5 / 11.99
		Requirement	≥10 N
		Conductor type	Type of conductor and conductor cross-section
			AWG 26/1
			AWG 26/19
		Evaluation	passed
		Requirement	≥20 N
		Conductor type	Type of conductor and conductor cross-section
			H05V-U0.75
			H05V-K0.75
		Evaluation	passed
		Requirement	≥40 N
		Conductor type	Type of conductor and conductor cross-section
			H07V-U1.5
			H07V-K1.5
			AWG 16/19
			AWG 26/1
			AWG 26/19

**B2CF 3.50/38/180 SN BK BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergsstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

	Type of conductor and conductor cross-section	H07V-K1.5
	Type of conductor and conductor cross-section	AWG 16/1
	Type of conductor and conductor cross-section	AWG 16/19
Evaluation	passed	

**Important note**

IPC conformity Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

## Notes

- Additional variants on request
- Gold-plated contact surfaces on request
- Rated current related to rated cross-section & min. No. of poles.
- Crimp shape A for wire-end ferrules with crimping tools PZ 1.5 (order no. 9005990000) or PZ 6/5 (order no. 9011460000) for larger wire cross-sections recommended.
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
- Max. outer diameter of the conductor 2.6 mm
- In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load
- Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months




**Classifications**

ETIM 8.0	EC002638	ETIM 9.0	EC002638
ETIM 10.0	EC002638	ECLASS 14.0	27-46-02-02
ECLASS 15.0	27-46-02-02		

**B2CF 3.50/38/180 SN BK BX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings****Product image****Graph****Product benefits**

Solid PUSH IN contactSafe and durable

## B2CF 3.50/38/180 SN BK BX

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Product benefits




Large connection cross-section  
Up to 1.5 mm<sup>2</sup> possible with ease

### Product benefits



Fast PUSH IN connection  
Tool-free and touch-safe

### Example of use



**B2CF 3.50/38/180 SN BK BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergsstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Accessories****Coding elements**

Only connects what is supposed to be connected: the right connection at the right place.

Coding elements and locking devices clearly assign connecting elements during the manufacturing process and operation

The coding elements and locking devices are inserted prior to assembly or during the cable assembly phase. The Weidmüller alternative: configure online using the variant configurator to precode prior to delivery.

Incorrect assembly on the circuit board and incorrect plugging of connecting elements is no longer possible. The advantage: no troubleshooting during manufacture and no operational errors by the user.

**General ordering data**

Type	B2L/S2L 3.50 KO BK BX	Version
Order No.	<a href="#">1849740000</a>	PCB plug-in connector, Accessories, Coding element, black, Number
GTIN (EAN)	4032248378203	of poles: 1
Qty.	100 ST	
Type	B2L/S2L 3.50 KO OR BX	Version
Order No.	<a href="#">1849730000</a>	PCB plug-in connector, Accessories, Coding element, orange, Number
GTIN (EAN)	4032248378197	of poles: 1
Qty.	100 ST	