

**WIL-LWXXXX-6500D012-240MFX5.0BCVPXXXX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



The WIL-LED lamp with car plug and magnet: Only 9.4mm high LED lamp for 12V DC with very high luminous efficacy and high Lifespan (greater 60 000h). Very robust construction, by full potting and metal housing - waterproof (IP67).

**General ordering data**

Order No.	2548620000
Type	<a href="#">WIL-LWXXXX-6500D012-240MFX5.0BCVPXXXX</a>
GTIN (EAN)	4050118558067
Qty.	1 items

## WIL-LWXXXX-6500D012-240MFX5.0BCVPXXXXX

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

## Approvals



RoHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate no. (cULus)	E354496

## Dimensions and weights

Depth	40 mm	Depth (inches)	1.5748 inch
Height	9.5 mm	Height (inches)	0.374 inch
Width	240 mm	Width (inches)	9.4488 inch
Net weight	100 g		

## Temperatures

Operating temperature	-20 - 60°C
-----------------------	------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%
EPREL Registration number	1326623

## Cable technical specifications

Cable Material	PUR	Sheathing colour	black
Housing main material	hard anodised aluminium	Cable length	5 m
Core cross-section	0.34 mm <sup>2</sup>		

## Connection data

LED Modul is attachable	no	Version	Car cigarette lighter
Number of poles	2	Connection thread	Miscellaneous

## Electric data

Rated voltage	12 V DC	Rated current	0,70 A
Power	8,5 W	Dimmable	Yes

## General technical data


Type of connection	Pre-assembled cable	Electronic equipment on rolling stock	No
Shape of the LED module	Rectangular	Number of LEDs	14
Light colour (CCT)	6500K, White	Luminosity	220 cd
Light current	886 lm	Emitting angle	40 °
Illumination level	291 lux	Operating life	60.000 h
Type of mounting	Magnet	Drill hole spacing	225 mm
Impact resistance	IK05	Protection degree	IP67
Efficiency class (according to EU Directive No. 874/2012)	Not required		

**WIL-LWXXXX-6500D012-240MFX5.0BCVPXXXX****Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Material data**

Material of LED cover	ESG	Housing main material	hard anodised aluminium
Material of end caps	PBT		

**Classifications**

ETIM 8.0	EC000996	ETIM 9.0	EC000996
ETIM 10.0	EC000996	ECLASS 14.0	27-11-06-35
ECLASS 15.0	27-11-06-35		


**Drawings****Dimensioned drawing**

**WIL-LWXXXX-6500D012-240MFX5.0BCVPXXXX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany


[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



## Accessories

### Screw terminal connector



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems. The screw connection can be used in a wide range of applications. With this technology the conductor, optionally with wire-end ferrules, can be plugged into connection elements and secured with a screw. It is the classic, cheapest form of connection technology that also supports multi-conductor connections.

### General ordering data

Type	SAIBGS-P-4A-4/6-M12	Version
Order No.	<a href="#">9457240000</a>	Field attachable connector, M12
GTIN (EAN)	4008190312275	
Qty.	1 ST	
Type	SAISGS-P-4A-4/6-M12	Version
Order No.	<a href="#">9457550000</a>	Field attachable connector, M12
GTIN (EAN)	4032248167647	
Qty.	1 ST	

### Motion sensor screw connection



Motion detector for the WIL-LED luminaire with screw connection. Switching time adjustable.

### General ordering data

Type	WIL-BM-SK	Version
Order No.	<a href="#">2537720000</a>	
GTIN (EAN)	4050118549157	
Qty.	1 ST	

**WIL-LWXXXX-6500D012-240MFX5.0BCVPXXXX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergsstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Accessories****Motion sensor screw connection with cable**

Motion detector for the WIL-LED luminaire with screw connection, 3m supply cable and M12 cable for connection to the WIL lamp. Switching time adjustable.

**General ordering data**

Type	WIL-BM-SK-M12-3.0U	Version
Order No.	<a href="#">2537700000</a>	
GTIN (EAN)	4050118549140	
Qty.	1 ST	

**Motion sensor Jackpac®**

Motion detector for the WIL-LED luminaire with screw connection, 3m supply cable and M12 cable for connection to the WIL lamp. Switching time adjustable.

**General ordering data**

Type	WIL-BM-JP-M12-3.0U	Version
Order No.	<a href="#">2537710000</a>	
GTIN (EAN)	4050118549164	
Qty.	1 ST	

**Door switch**

The WIL door switch is pre-assembled with an M12 cable and an access line. This allows for a simple Plug and Produce feature with our WIL LED lamp series.

**Door Switch****General ordering data**

Type	WIL-TS-M12	Version
Order No.	<a href="#">2537730000</a>	
GTIN (EAN)	4050118549188	
Qty.	1 ST	

**WIL-LWXXXX-6500D012-240MFX5.0BCVPXXXX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergsstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Accessories****Swivelling holder**

Swivel bracket for WIL lights Very high quality version without detent

**Swivelling holder****General ordering data**

Type WIL-SCHWENKHALTER

Version

Order No. [2614220000](#)

GTIN (EAN) 4050118651249

Qty. 1 ST

**Connect Power INSTA POWER**

The single-phase INSTA-POWER switching power supplies are characterised by a wide power spectrum, compact design and good value for money. They are suitable for temperature ranges from -25°C to +70°C, have international approvals and a wide voltage input range. This makes them suitable for a wide range of applications. This also includes signal and telecommunications systems as well as automation systems with a low power requirement up to 96 Watt.

**General ordering data**

Type PRO INSTA 30W 24V 1.3A

Version

Order No. [2580190000](#)

Power supply, switch-mode power supply unit, 24 V

GTIN (EAN) 4050118590920

Qty. 1 ST