


**WQB 12 WTL 6/4 FF**
**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**


The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, orange, 41 A, Number of poles: 12, Pitch in mm (P): 11.10, Insulated: Yes, Width: 129.1 mm
Order No.	<a href="#">2552080000</a>
Type	WQB 12 WTL 6/4 FF
GTIN (EAN)	4050118577655
Qty.	10 items
Delivery status	This article will no longer be available in the future.
Last order date	2026-09-30T00:00:00+02:00

## WQB 12 WTL 6/4 FF

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	5 mm	Depth (inches)	0.1968 inch
Height	29.32 mm	Height (inches)	1.1543 inch
Width	129.1 mm	Width (inches)	5.0827 inch
Net weight	24.11 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Basic material	Wemid	Colour	orange
----------------	-------	--------	--------

### System specifications

Version	Cross-connector
---------	-----------------

### Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No	Type of mounting	when screwed in

### Dimensions

Pitch in mm (P)	11.10 mm
-----------------	----------

### General

Number of poles	12	Installation advice	Direct mounting
-----------------	----	---------------------	-----------------

### Rating data

Rated voltage	400 V	Nominal current	41 A
---------------	-------	-----------------	------

### Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		