

**CMA-CTM-7-64-1A-0.5VA-1**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

similar to the product

The CMA-CTM 7 series mini current transformer is an inductive current transformer designed according to the transformer principle for circular primary conductors.

The CMA-CTM 7 series current transformers are maintenance-free and is designed for measuring primary currents in the range 32 A to 64 A. This is converted into a current up to 1 A on the secondary side.

With its small dimensions, it perfectly suits applications in a 3-phase circuit breaker with a phase separation of 17.5 mm.

**General ordering data**

Version	Primary current: 64 A, Secondary current max.: 1 A, Load: 0.5 VA, Tolerance class: 1, closed current transformer
Order No.	<a href="#">2556010000</a>
Type	CMA-CTM-7-64-1A-0.5VA-1
GTIN (EAN)	4050118566079
Qty.	1 items
Manufacturer	MBS AG

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Depth	19 mm	Depth (inches)	0.748 inch
Height	46.5 mm	Height (inches)	1.8307 inch
Width	27.5 mm	Width (inches)	1.0827 inch
Net weight	65 g		

**Temperatures**

Storage temperature	-25 °C...70 °C	Operating temperature	-5 °C...50 °C
---------------------	----------------	-----------------------	---------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

**Dimensions of live conductors**

Type of conductor	Insulated conductor only	Round conductor	7.60 mm
Installation location	Indoor use		

**Electrical attributes**

Tolerance class	1	Secondary current	0...1 A
Load	0.5 VA	Primary current	64 A

**Technical properties**

Insulation class	E	Thermal rated continuous current I <sub>thermal</sub>	1.0 x I <sub>rated</sub>
Nominal frequency	50 Hz		

**Insulation coordination**

Standard	IEC 61869-1: 2007, IEC 61869-2: 2012	Tolerance class	1
----------	--------------------------------------	-----------------	---

**Classifications**



ETIM 8.0	EC002048	ETIM 9.0	EC002048
ETIM 10.0	EC002048	ECLASS 14.0	27-21-09-02
ECLASS 15.0	27-21-09-02		

CMA-CTM-7-64-1A-0.5VA-1

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

Drawings

[www.weidmueller.com](http://www.weidmueller.com)



**CMA-CTM-7-64-1A-0.5VA-1**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Accessories****Mini current transformer**

The CMA-CTM 7 series mini current transformer is an inductive current transformer designed according to the transformer principle for circular primary conductors.

The CMA-CTM 7 series current transformers are maintenance-free and is designed for measuring primary currents in the range 32 A to 64 A. This is converted into a current up to 1 A on the secondary side.

With its small dimensions, it perfectly suits applications in a 3-phase circuit breaker with a phase separation of 17.5 mm.

**General ordering data**

Type	CMA-CTM-7-SNAP-ON	Version	
Order No.	<a href="#">2525 160000</a>		
GTIN (EAN)	4050118536522		
Qty.	1 ST		