

HDC MBUS8 M AWG20

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Compact

The new two-pole bus module is extremely compact and can accommodate both megabit and gigabit data inserts. It enables the connection of 2 Gigabit Cat 6A cables (10 gigabit) to one module.

General ordering data

Version	Crimp contact
Order No.	2565980000
Type	HDC MBUS8 M AWG20
GTIN (EAN)	4050118575835
Qty.	100 items

HDC MBUS8 M AWG20

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Net weight 0 g

Temperatures

Limit temperature -40 °C ... 90 °C

Environmental Product Compliance

RoHS Compliance Status Compliant with exemption
 RoHS Exemption (if applicable/known) 6c
 REACH SVHC Lead 7439-92-1
 SCIP 6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

General data

Contact diameter, male Ø	0.6 mm	Stripping length, rated connection	4 mm
Type of connection	Crimp connection	Version insert	MBUS
Conductor cross-section, max.	0.5 mm ²	Conductor cross-section, min.	0.5 mm ²
Surface finish	gold	Plugging cycles	≥ 500
Type	Male	Basic material	Copper alloy
Series	ModuPlug	Production methods	turned
Material of contact	Copper alloy		

General data

Contact surface	Gold-plated	Transmission rate	10 Gbps
Nominal current	0.5 A	Plugging cycles	≥ 500
Type	Male		

Classifications

ETIM 8.0	EC000796	ETIM 9.0	EC000796
ETIM 10.0	EC000796	ECLASS 14.0	27-44-02-04
ECLASS 15.0	27-44-02-04		

HDC MBUS8 M AWG20

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

