

PRO INSTA 96W 48V 2A

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The single-phase INSTA-POWER switching power supplies are characterised by a wide power spectrum, compact design and good value for money. They are suitable for temperature ranges from -25°C to $+70^{\circ}\text{C}$, have international approvals and a wide voltage input range. This makes them suitable for a wide range of applications. This also includes signal and telecommunications systems as well as automation systems with a low power requirement up to 96 Watt.

General ordering data

Version	Power supply, switch-mode power supply unit, 48 V
Order No.	2580270000
Type	PRO INSTA 96W 48V 2A
GTIN (EAN)	4050118591002
Qty.	1 items

PRO INSTA 96W 48V 2A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform
 UL File Number Search [UL Website](#)
 Certificate no. (cULus) E258476

Dimensions and weights

Depth	60 mm	Depth (inches)	2.3622 inch
Height	90 mm	Height (inches)	3.5433 inch
Width	90 mm	Width (inches)	3.5433 inch
Net weight	361 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-25 °C...70 °C
Start-up	≥ -40 °C		

Environmental Product Compliance

RoHS Compliance Status Compliant with exemption
 RoHS Exemption (if applicable/known) 6c, 7a, 7cI
 REACH SVHC Lead 7439-92-1, Lead monoxide 1317-36-8
 SCIP d62541f7-8058-4336-b693-7303c8b40800

Input

Connection system	PUSH IN with actuator	AC input voltage range	85...264 V AC (derating at 100 V AC)
Recommended back-up fuse	2 A / DI, safety fuse 6 A, Char. B, circuit breaker 2...4 A, Char. C circuit breaker	Frequency range AC	45...65 Hz
Rated input voltage	110...240 V AC / 120...340 V DC	Wire connection method	PUSH IN with actuator
Input fuse (internal)	Yes	AC current consumption	1.2 A @ 230 V AC / 2.5 A @ 100 V AC
DC current consumption	0.4 A @ 370 V DC / 1.35 A @ 120 V DC	DC input voltage range	95...370 V DC
Inrush current	max. 40 A	Nominal power consumption	107.9 VA

Output

Output power	96 W	Connection system	PUSH IN
Rated output voltage	48 V DC ± 1 %	Residual ripple, breaking spikes	<50 mVss @ UNenn, Full Load
Output voltage, max.	56 V	Output voltage, min.	35 V
Output current, max.	2 A	Wire connection method	PUSH IN with actuator
Output voltage, note	(adjustable via potentiometer on front)	Nominal output current for Unom	2 A @ 55 °C
Capacitive load	unrestricted	Continuous output current @ UNominal °C	2 A @ 55 °C, 1.25 A @ 70 °C
Ramp-up time	≤ 100 ms		

PRO INSTA 96W 48V 2A

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

General data

Degree of efficiency	89%	Protection degree	IP20
Mounting position, installation notice	Horizontal on DIN rail TS 35, top and bottom 50 mm clearance for free air flow, 10 mm clearance to neighbouring active subassemblies with full load, 5 mm with passive neighbouring subassemblies, direct row mounting with 90% rated load	Housing version	Plastic, protective insulation
Protection against reverse voltages from the load	58...62 V DC	Power loss, idling	0.45 W
Short-circuit protection	Yes, internal	Power loss, nominal load	10.56 W

EMC / shock / vibration

Limiting of mains voltage harmonic currents	EN 61000-4-2 (ESD)/EN 61000-4-3 and EN 61000-4-8 (fields)/EN 61000-4-4 (burst)/EN 61000-4-5 (surge)/EN 61000-4-6 (conducted)/EN 61000-4-11 (dips), EN 61000-4-11 (Dips)	Shock resistance IEC 60068-2-27	15 g In all directions
Noise emission in accordance with EN55032	Class B	Interference immunity test acc. to	EN 61000-4-2 (ESD)/EN 61000-4-3 and EN 61000-4-8 (fields)/EN 61000-4-4 (burst)/EN 61000-4-5 (surge)/EN 61000-4-6 (conducted)/EN 61000-4-11 (dips), EN 61000-4-11 (Dips)
Vibration resistance IEC 60068-2-6	2.3 g		

Insulation coordination

Pollution severity	2	Protection class	II
Insulation voltage, input/output	4 kV	Insulation voltage input / earth	3.5 kV
Insulation voltage output / earth	0.5 kV		

Electrical safety (applied standards)

Electrical machine equipment	Acc. to EN60204	Safety extra-low voltage	SELV acc. to IEC 61010-1, PELV acc. to IEC 61010-2-201
Safety transformers for switch-mode power supplies	According to EN 61558-2-16		

Connection data (input)

Connection system	PUSH IN with actuator	Number of terminals	2 (L,N)
Conductor cross-section, AWG/kcmil , max.	12 AWG	Conductor cross-section, AWG/kcmil , min.	24 AWG
Wire connection cross section, flexible (input), max.	2.5 mm ²	Conductor cross-section, flexible , min.	0.25 mm ²
Conductor cross-section, rigid , max.	2.5 mm ²	Conductor cross-section, rigid , min.	0.25 mm ²

PRO INSTA 96W 48V 2A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Connection data (output)

Connection system	PUSH IN	Number of terminals	4 (++ / -)
Conductor cross-section, AWG/kcmil , max.	12 AWG	Conductor cross-section, AWG/kcmil , min.	24 AWG
Conductor cross-section, flexible , max.	2.5 mm ²	Conductor cross-section, flexible , min.	0.25 mm ²
Conductor cross-section, rigid , max.	2.5 mm ²	Conductor cross-section, rigid , min.	0.25 mm ²

Signalling

LED green	Operating voltage OK
-----------	----------------------

Classifications


ETIM 8.0	EC002540	ETIM 9.0	EC002540
ETIM 10.0	EC002540	ECLASS 14.0	27-04-07-01
ECLASS 15.0	27-04-07-01		

PRO INSTA 96W 48V 2A

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



PRO INSTA 96W 48V 2A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

End bracket




Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

Type	WEW 35/1 V0 GF SW	Version	
Order No.	1478990000	End bracket, black, TS 35, V-0, Wemid, Width: 12 mm, 130 °C	
GTIN (EAN)	4050118286892		
Qty.	50 ST		
Type	WEW 35/2 V0 GF SW	Version	
Order No.	1479000000	End bracket, black, TS 35, V-0, Wemid, Width: 8 mm, 130 °C	
GTIN (EAN)	4050118286779		
Qty.	50 ST		

Slotted screwdriver



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Type	SDIS SL 0.6X3.5X100	Version	
Order No.	1274660000	Screwdriver, Mounting tool	
GTIN (EAN)	4050118072631		
Qty.	1 ST		