# **CABTITE SE 25-26 LRG BK**



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com







Whether a large or small cable diameter – Cabtite always offers the right seal insert.

The conical shape of the sealing elements allows the previously positioned snap-in grid inlays to be pushed in easily from the inside to the outsid. It reliably seals intermediate spaces and provides strain relief in accordance with DIN EN 62444. The seal inserts combined with the frames achieve an IP 66 degree of protection. As a result of its slotted design with wave cut, it is especially suitable for pre-assembled cables.

- The black seal inserts are designed for a particularly high operating temperature and offer fire safety class UL 94 HB
- The grey sealing elements comply with fire safety class UL 94 VO and are therefore suitable for the demands of the railway industry
- By using multiple inserts, two or more cables, as well as special cables, can be passed through a sealing element

#### **General ordering data**

Version	Sealing element, Cabtite (cable entry system), TPE, Deep black, Height: 42.8 mm, Width: 42.8 mm, Depth: 17.7 mm, -40 °C120 °C, IP66	
Order No.	<u>2583700000</u>	
Туре	CABTITE SE 25-26 LRG BK	
GTIN (EAN)	4050118617207	
Qty.	10 items	

1



# **CABTITE SE 25-26 LRG BK**



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

Аp	pro	oval	S
----	-----	------	---

Approvals	
	C C 2 110

ROHS	Conform
UL File Number Search	<u>UL Website</u>
Certificate No. (cURus)	E223801

# **Dimensions and weights**

Depth	17.7 mm	Depth (inches)	0.6968 inch
Height	42.8 mm	Height (inches)	1.685 inch
Width	42.8 mm	Width (inches)	1.685 inch
Net weight	19.98 g		

## **Temperatures**

Operating temperature -40 °C...120 °C

## **Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## **General information**

Outer cable diameter, max.	26 mm	Outer cable diameter, min.	25 mm
Silicone	No	UL 94 flammability rating	НВ
Halogen	No	Protection degree	IP66
Basic material	TPE	Sealing element	1 large sealing element

## Classifications

ETIM 6.0	EC000879	ETIM 7.0	EC000879
ETIM 8.0	EC000879	ETIM 9.0	EC000879
ETIM 10.0	EC000879	ECLASS 9.0	27-14-44-21
ECLASS 9.1	27-14-44-21	ECLASS 10.0	27-14-44-21
ECLASS 11.0	27-14-44-21	ECLASS 12.0	27-14-08-07
ECLASS 13.0	27-14-08-07	ECLASS 14.0	27-14-08-07
ECLASS 15.0	27-14-08-07		
ECLASS 11.0 ECLASS 13.0	27-14-44-21 27-14-08-07	ECLASS 12.0	27-14-08-07

Catalogue status / Drawings 2