



VPU AC II 0 350/50

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



In the event of a defective arrester, you can easily reorder this spare arrester, replace the defective arrester and thus restore protection.

General ordering data

| | |
|------------|--|
| Version | Spare arrester, Surge protection, Single-phase, TN |
| Order No. | 2591340000 |
| Type | VPU AC II 0 350/50 |
| GTIN (EAN) | 4050118599596 |
| Qty. | 1 items |

VPU AC II 0 350/50

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-------------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E3542610000 |

Dimensions and weights

| | | | |
|------------|-------|-----------------|-------------|
| Depth | 64 mm | Depth (inches) | 2.5197 inch |
| Height | 45 mm | Height (inches) | 1.7716 inch |
| Width | 18 mm | Width (inches) | 0.7087 inch |
| Net weight | 64 g | | |

Temperatures

| | | | |
|-----------------------|----------------|---------------------|-----------------------|
| Storage temperature | -40 °C...85 °C | Ambient temperature | -40 °C...85 °C |
| Operating temperature | -40 °C...85 °C | Humidity | 5 - 95% rel. humidity |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Rated data UL

| | | |
|---|--|--------|
| Ambient temperature (operational), max. 85 °C | Rated Voltage UN | 277 V |
| VPR (N-PE) | MCOV (L/N-PE) | 350 V |
| SCCR | In | 20 kA |
| Category | Ambient temperature (operational), min. -40 °C | |
| Certificate No. (cURus) | VPR (L-PE) | 1000 V |
| Voltage type | AC | |

Connection data, remote alert

| | |
|-----------------|---------|
| Connection type | PUSH IN |
|-----------------|---------|

General data

| | | | |
|---------------------------|---|---------------|---------------------------|
| Optical function display | green = OK; red = arrester is defective - replace | Segment | Power distribution |
| Version | Surge protection | Design | Installation housing; 1TE |
| UL 94 flammability rating | V-0 | Colour | orange |
| Protection degree | IP20 in installed state | Mounting rail | TS 35 |
| Operating altitude | ≤ 2000 m, ≤ 4000 m | | |

Rated data IEC / EN

| | | | |
|-----------------------|--------|---------------------|-----------------------------|
| Number of poles | 1 | Combined pulse UOC | 6 kV |
| Leakage current at Un | 0.3 mA | Signalling contact | No |
| Rated voltage (AC) | 230 V | Low voltage network | Single-phase, TN |
| Voltage type | AC | Fuse protection | No Fuse necessary ≤315 A gG |

VPU AC II 0 350/50

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

| | | | |
|---|-----------|--|---|
| Response time / fallback time | ≤ 25 ns | Frequency range, max. | 60 Hz |
| Frequency range, min. | 50 Hz | Standards | IEC61643-11, EN61643-11, UL 1449, IEC 61643-11, EN 61643-11 |
| Requirements class, acc. to EN 61643-11 | T2, T3 | Requirements category acc. to IEC 61643-11 | Type II, Type III |
| Max. continuous voltage, U _c (AC) | 350 V | Energy coordination (≤10 m) | Type II, Type III |
| Discharge current I _n (8/20μs) wire-PE | 20 kA | Discharge current I _{max} (8/20μs) wire-PE | 50 kA |
| Protection level Up at IN (L/N-PE) | ≤ 1.75 kV | Short-circuit current rating ISCCR | 15 kA |
| Discharge current (type III) | 3 kA | Follow-on current extinguishing capability I _{fi} | Follow current need not be taken into account |
| Integrated back-up fuse | No | | |

Connection data

| | | | |
|--|---------------------|---------------------------------|--------------------------------------|
| Stripping length | 18 mm | Type of connection | Plug-in connection, Screw connection |
| Wire cross-section, solid, min. | 1.5 mm ² | Wire cross-section, solid, max. | 35 mm ² |
| Wire connection cross section, finely stranded, max. | 25 mm ² | | |

Electrical data

| | |
|--------------|----|
| Voltage type | AC |
|--------------|----|

General data

| | | | |
|-----------------|--------|-------------------|-------------------------|
| Number of poles | 1 | Protection degree | IP20 in installed state |
| Colour | orange | | |

Guarantee


| | |
|---------------|---------|
| Time interval | 5 years |
|---------------|---------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000941 | ETIM 9.0 | EC000941 |
| ETIM 10.0 | EC000941 | ECLASS 14.0 | 27-17-12-02 |
| ECLASS 15.0 | 27-17-12-02 | | |

Drawings

Electric symbol



Schematic circuit diagram

VPU AC II 0 350/50

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Slotted screwdriver




VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

General ordering data

| | | | |
|------------|----------------------------|---|--|
| Type | SDIS 1.0X5.5X125 | Version | |
| Order No. | 2749850000 | Screwdriver, Blade width (B): 5.5 mm, Blade length: 125 mm, Blade thickness (A): 1 mm | |
| GTIN (EAN) | 4050118897050 | | |
| Qty. | 1 ST | | |

Blank



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | ESG 6/15 K MC NE WS | Version | |
| Order No. | 1880100000 | ESG, Device markers x 15 mm, PA 66, Colour: white, Self-adhesive | |
| GTIN (EAN) | 4032248478781 | | |
| Qty. | 200 ST | | |

VPU Series



Extensive accessories round off the product range

VPU AC II 0 350/50

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

General ordering data

| | | | |
|------------|----------------------------|---------|--|
| Type | VPU LOCKING CLIP S | Version | |
| Order No. | 2735080000 | | |
| GTIN (EAN) | 4050118826050 | | |
| Qty. | 10 ST | | |