

PRO TOP1 120W 24V 5A F

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Illustration similar

Production processes constantly need to be made more efficient. As well as performance, energy efficiency and sustainability are also playing an increasingly important role in cutting-edge industry. PROtop power supplies combine excellent performance data with exemplary sustainability, which has a positive impact on the productivity of the entire production facility.

PROtop offers a number of advantages that give you a real competitive edge. These include the permanent reduction of energy costs thanks to high efficiencies as well as the increase in plant availability due to long service life and high MTBF values. In addition, there is a high functional density due to the extremely spacesaving designs.

PROtop can achieve significant savings compared to conventional power supply units. Its increased efficiency saves an average of 50 kWh per day in a medium-sized production facility with approx. 100 PROtop power supplies working in three-shift operation. This adds up to over 15,000 kWh a year and also improves the facility's carbon footprint. The service life, which is twice as long as that of standard power supplies, also sustainably reduces the costs of repurchase and exchange.

General ordering data

| | |
|------------|---|
| Version | Power supply, switch-mode power supply unit, 24 V |
| Order No. | 2568980000 |
| Type | PRO TOP1 120W 24V 5A F |
| GTIN (EAN) | 4050118579703 |
| Qty. | 1 items |

PRO TOP1 120W 24V 5A F

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|---------------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E255651 |
| Certificate no. (cULusEX) | E470829 |

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 125 mm | Depth (inches) | 4.9212 inch |
| Height | 130 mm | Height (inches) | 5.1181 inch |
| Width | 35 mm | Width (inches) | 1.378 inch |
| Net weight | 850 g | | |

Temperatures

| | | | |
|-----------------------------------|---------------------------|-----------------------|----------------|
| Storage temperature | -40 °C...85 °C | Operating temperature | -25 °C...70 °C |
| Humidity at operating temperature | 5...95 %, no condensation | Start-up | ≥ -40 °C |

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c, 7a, 7cl |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 6d8cdf22-8230-4af8-86c8-3558c716666d |

Input

| | | |
|--|--|-------|
| Connection system | PUSH IN with actuator | |
| AC input voltage range | 85...277 V AC | |
| Recommended back-up fuse | 5 A, DI / 6 A, Char. B / 6 A, Char C | |
| Frequency range AC | 45...65 Hz | |
| Rated input voltage | 110...240 V AC / 120...340 V DC | |
| Surge protection | Varistor | |
| Input fuse (internal) | Yes | |
| DC input voltage range | 48...410 V DC (Derating 40% @ 48 V DC) | |
| Inrush current | max. 5 A | |
| Current consumption in relation to the input voltage | Voltage type | AC |
| | Input voltage | 100 V |
| | Input current | 2 A |
| | Voltage type | DC |
| | Input voltage | 120 V |
| | Input current | 2 A |
| Nominal power consumption | 131.9 VA | |

Output

| | |
|--------------------------------|----------------------------|
| Output power | 120 W |
| Mains failure bridge-over time | > 20 ms @ 115V AC/ 230 VAC |

PRO TOP1 120W 24V 5A F

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

| | | | |
|------------------------------------|--|-------|--|
| Connection system | PUSH IN with actuator | | |
| Rated output voltage | 24 V DC \pm 1 % | | |
| Residual ripple, breaking spikes | <50 mVss @ UNenn, Full Load | | |
| Parallel connection option | Yes, for redundancy and power increase (with ORing MOSFET) | | |
| Output voltage, max. | 28.8 V | | |
| Output voltage, min. | 22.5 V | | |
| Output current, max. | 5 A | | |
| Output voltage, note | adjustable with potentiometer or communication module | | |
| Nominal output current for Unom | 5 A @ 60 °C | | |
| Protection against inverse voltage | Yes | | |
| DCL - peak load reserve | Boost duration | 5 s | |
| | Multiple of the rated current | 150 % | |
| | Boost duration | 15 ms | |
| | Multiple of the rated current | 600 % | |
| Ramp-up time | \leq 100 ms | | |

General data

| | | | |
|-----------------------------|----------------------------|--|--|
| Power factor (approx.) | > 0.85 | AC failure bridging time @ Inom | > 20 ms @ 230 V AC / > 20 ms @ 115 V AC |
| Degree of efficiency | 91% | Protection degree | IP20 |
| Surge voltage category | III, II | Mounting position, installation notice | Horizontal on DIN rail TS 35, top and bottom 50 mm clearance for free air flow, 10 mm clearance to neighbouring subassemblies. |
| Housing version | Metal, corrosion resistant | Derating | > 60°C (2.5% / 1°C) |
| Earth leakage current, max. | 3.5 mA | Conformal coating | No |
| Power loss, idling | 5 W | Short-circuit protection | Yes, internal |
| Power loss, nominal load | 11.8 W | | |

EMC / shock / vibration

| | | | |
|------------------------------------|--|---|---|
| Shock resistance IEC 60068-2-27 | 30 g in all directions | Noise emission in accordance with EN55032 | Class B |
| Interference immunity test acc. to | EN 55032:2015, EN 55024:2010/A1:2015, EN 55035:2017, EN 61000-3-2:2014, EN 61000-6-1:2007, EN 61000-6-2:2005, EN 61000-6-3:2007/A1:2011, EN 61000-6-4:2007/A1:2011 | Vibration resistance IEC 60068-2-6 | 2.3 g (on DIN rail), 4 g (with direct mounting) |

Insulation coordination

| | | | |
|----------------------------------|-----------------------|-----------------------------------|--------|
| Surge voltage category | III, II | Pollution severity | 2 |
| Protection class | I, with PE connection | Insulation voltage, input/output | 3.5 kV |
| Insulation voltage input / earth | 3.2 kV | Insulation voltage output / earth | 0.5 kV |

Electrical safety (applied standards)

| | | | |
|--|----------------------------|--------------------------|--|
| Electrical machine equipment | Acc. to EN60204 | Safety extra-low voltage | SELV acc. to IEC 60950-1, PELV according to EN 60204-1 |
| Safety transformers for switch-mode power supplies | According to EN 61558-2-16 | | |

PRO TOP1 120W 24V 5A F

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Connection data (input)

| | | | |
|---|-----------------------|---|---------------------|
| Connection system | PUSH IN with actuator | Number of terminals | 3 for L/N/PE |
| Screwdriver blade | 0.6 x 3.5 | Conductor cross-section, AWG/kcmil , max. | 12 AWG |
| Conductor cross-section, AWG/kcmil , min. | 20 AWG | Wire connection cross section, flexible (input), max. | 2.5 mm ² |
| Conductor cross-section, flexible , min. | 0.5 mm ² | Conductor cross-section, rigid , max. | 1.5 mm ² |
| Conductor cross-section, rigid , min. | 0.5 mm ² | | |

Connection data (output)

| | | | |
|---|-----------------------|---|---------------------|
| Connection system | PUSH IN with actuator | Number of terminals | 4 (++ / -) |
| Conductor cross-section, AWG/kcmil , max. | 12 AWG | Conductor cross-section, AWG/kcmil , min. | 26 AWG |
| Conductor cross-section, flexible , max. | 2.5 mm ² | Conductor cross-section, flexible , min. | 0.2 mm ² |
| Conductor cross-section, rigid , max. | 2.5 mm ² | Conductor cross-section, rigid , min. | 0.2 mm ² |
| Screwdriver blade | 0.6 x 3.5 | | |

Connection data (signal)

| | | | |
|--|---------------------|--|----------------------|
| Wire connection cross-section, flexible (signal), max. | 1.5 mm ² | Wire connection method | PUSH IN |
| Wire cross-section, AWG/kcmil , max. | 16 | Wire cross-section, solid , min. | 0.14 mm ² |
| Wire cross-section, solid , max. | 1.5 mm ² | Wire connection cross-section, flexible (signal), min. | 0.14 mm ² |
| Wire cross-section, AWG/kcmil , min. | 26 mm ² | | |

Signalling

| | | | |
|--------------------------|-----------------------------------|---------------|---|
| Floating contact | Yes | LED green/red | Green: Operation (failure-free), Flashing green: advance warning I>90%, Green/red flashing: output switched off (switch-off mode), Flashing red: overload/error |
| Status relay (max. load) | Output voltage OK (30 V DC / 1 A) | | |



Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002540 | ETIM 9.0 | EC002540 |
| ETIM 10.0 | EC002540 | ECLASS 14.0 | 27-04-07-01 |
| ECLASS 15.0 | 27-04-07-01 | | |

PRO TOP1 120W 24V 5A F

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

PRO TOP1 120W 24V 5A F

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**End bracket**

Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | WEW 35/1 VO GF SW | Version |
| Order No. | 1478990000 | End bracket, black, TS 35, V-0, Wemid, Width: 12 mm, 130 °C |
| GTIN (EAN) | 4050118286892 | |
| Qty. | 50 ST | |
| Type | WEW 35/2 VO GF SW | Version |
| Order No. | 1479000000 | End bracket, black, TS 35, V-0, Wemid, Width: 8 mm, 130 °C |
| GTIN (EAN) | 4050118286779 | |
| Qty. | 50 ST | |

Slotted screwdriver

VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | SDIS SLIM 0.6X3.5X100 | Version |
| Order No. | 2749610000 | Mounting tool, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade |
| GTIN (EAN) | 4050118896350 | thickness (A): 0.6 mm |
| Qty. | 1 ST | |

Installation

Mounting accessory for Weidmüller Power Supplys.

PRO TOP1 120W 24V 5A F

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

General ordering data

| | | |
|------------|----------------------------|---------------------------------------|
| Type | PRO TOP BRACKETS | Version |
| Order No. | 2575900000 | Mounting foot |
| GTIN (EAN) | 4050118683059 | |
| Qty. | 1 ST | |
| Type | MTA 30 MF | Version |
| Order No. | 1251320000 | Electronics housings, Mounting flange |
| GTIN (EAN) | 4050118042702 | |
| Qty. | 20 ST | |
| Type | CP A WALLADAPTER 30 MM | Version |
| Order No. | 1461870000 | |
| GTIN (EAN) | 4050118268225 | |
| Qty. | 1 ST | |

Communication modules



Weidmüller's plug-in communication modules enable individual components to exchange relevant data with the cloud. This lays the foundation for targeted process optimization using condition monitoring and remote controllability - factors that play a decisive role in increasing efficiency, quality, process stability and availability can contribute. The communication modules are designed according to IP20 protected, can be operated without tools and can be flexibly adapted to different customisable communication protocols.

General ordering data

| | | |
|------------|----------------------------|----------------------|
| Type | PRO COM CAN OPEN | Version |
| Order No. | 2467320000 | Communication module |
| GTIN (EAN) | 4050118482225 | |
| Qty. | 1 ST | |
| Type | PRO COM CAN OPEN EX | Version |
| Order No. | 2467340000 | Communication module |
| GTIN (EAN) | 4050118481822 | |
| Qty. | 1 ST | |
| Type | PRO COM DISPLAY 7S | Version |
| Order No. | 2466960000 | Communication module |
| GTIN (EAN) | 4050118481808 | |
| Qty. | 1 ST | |
| Type | PRO COM IO-LINK | Version |
| Order No. | 2587360000 | Communication module |
| GTIN (EAN) | 4050118599152 | |
| Qty. | 1 ST | |

PRO TOP1 120W 24V 5A F

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

BLF 5.08HC/180F SN



Just as reliable as the millionfold proven original and featuring innovative details:

The BLF 5.08HC PUSH IN version of the BLZP 5.08HC female connector is not only different in terms of connection system; it also has a more compact design. Weidmüller's innovative PUSH IN spring connection system stands for the future of easy and tool-free wire connection. HC = High Current.


In terms of versatility, the BLF 5.08HC offers just as much as the version which served as a model:

- 3 tested-and-proven wire outlet directions provide the usual flexibility for application-specific design
- 4 flange variations and the patented release latch allow the locking concept to be based on the requirements of the user
- Use the BLF 5.08HC and SL 5.08HC plug combination to reach the max. rated specifications

General ordering data

| | | |
|------------|----------------------------|--|
| Type | BLF 5.08HC/03/180F SN B... | Version |
| Order No. | 1012650000 | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 3, |
| GTIN (EAN) | 4032248720309 | 180°, PUSH IN with actuator, Clamping range, max. : 3.31 mm ² , Box |
| Qty. | 72 ST | |

BCF 3.81/180F



PUSH IN - Weidmüller's innovative connection system simplifies the wire connection process.

The benefits for users and applications:

- High packaging density due to very low component height. Simply insert the prepared wire - finished
- High component density with the compact SCDN / SCDN-THR two-tier pin header
- Simplified processing due to integrated push buttons for opening the clamping unit
- Intuitive handling – since the wire-entry area and handling area are clearly separated
- tool-free locking and releasing when using Weidmüller's patented release latch (LR)

The Weidmüller plug-in connectors, pitch 3.81 mm (0.15 inch), are compatible with the layout of customary plug-in connectors, can be coded and provide space for printing.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | BCF 3.81/03/180F SN BK ... | Version |
| Order No. | 1347850000 | PCB plug-in connector, female plug, 3.81 mm, Number of poles: 3, |
| GTIN (EAN) | 4050118152517 | 180°, PUSH IN with push button, Clamping range, max. : 1.5 mm ² , |
| Qty. | 50 ST | Box |

PRO TOP1 120W 24V 5A F

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

Accessories

www.weidmueller.com

BLF 5.00HC/180F SN



Just as reliable as the millionfold proven original and featuring innovative details:

The BLF 5.00HC PUSH IN version of the BLZ 5.00HC female connector features a new connection system and a more compact design. Weidmüller's innovative PUSH IN spring connection system stands for the future of easy and tool-free wire connection. HC = High Current.

In terms of versatility, the BLF 5.00HC offers just as much as the older versions:

- 3 tested-and-proven wire outlet directions provide the usual flexibility for application-specific design
- 4 flange variations and the patented release latch allow the locking concept to be based on the requirements of the user

General ordering data

| | | |
|------------|----------------------------|--|
| Type | BLF 5.00HC/04/180F SN B... | Version |
| Order No. | 2568270000 | PCB plug-in connector, female plug, 5.00 mm, Number of poles: 4, |
| GTIN (EAN) | 4050118578805 | 180°, PUSH IN with actuator, Clamping range, max. : 3.31 mm ² , Box |
| Qty. | 72 ST | |