

**THM WO 50/100 SI****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

**General ordering data**

Version	THM, Conductor and cable markers, 7 - 23 mm, 50 x 100 mm, silver
Order No.	<a href="#">2596610000</a>
Type	THM WO 50/100 SI
GTIN (EAN)	4050118660852
Qty.	1000 items

## THM WO 50/100 SI

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	0.03 mm	Depth (inches)	0.001 inch
Height	50 mm	Height (inches)	1.9685 inch
Width	100 mm	Width (inches)	3.937 inch
Net weight	0.75 g		

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## General data

Adhesive	Polyacrylate adhesive	
Orientation of print	horizontal and vertical	
Type of printing	neutral	
Width	100 mm	
UL 94 flammability rating	V-0	
Colour	silver	
Halogen	No	
Basic material	Polyethylene	
Printed characters	without	
Number of markers per packaging unit	Form of supply	Label reel
compatible printer		
Number of markers per combination	1 Label reel = Conductor and cable markers	
Number per roll	1000	

## Conductor and cable markers

Halogen	No	Conductor cross-section, max.	444 mm <sup>2</sup>
Conductor O.D., max.	23 mm	Conductor O.D., min.	7 mm
Text field width	50 mm	Text field height	25 mm
Conductor O.D.	7 - 23 mm	Cross-section for connected wire	444 mm <sup>2</sup>

## Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

