

ERTE KLBC SPX 10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

| | |
|------------|---------------------------------------|
| Version | Accessories, Replacement clamping jaw |
| Order No. | 2571480000 |
| Type | ERTE KLBC SPX 10 |
| GTIN (EAN) | 4050118582109 |
| Qty. | 1 items |

ERTE KLBC SPX 10

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 21 mm | Depth (inches) | 0.8268 inch |
| Height | 40 mm | Height (inches) | 1.5748 inch |
| Width | 91 mm | Width (inches) | 3.5827 inch |
| Net weight | 22.5 g | | |

Environmental Product Compliance

| | |
|------------------------|--------------------------------------|
| RoHS Compliance Status | Not affected |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 6a3438d7-aa8c-48e4-8879-adf736ca79e3 |

Technical data

| | |
|------------------------|-----------------------------|
| Description of article | Clamping jaw for Stripax 10 |
|------------------------|-----------------------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002691 | ETIM 9.0 | EC002691 |
| ETIM 10.0 | EC002691 | ECLASS 14.0 | 21-04-51-92 |
| ECLASS 15.0 | 21-04-51-92 | | |