

## ENERGY ANALYSER 550-24

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



### Energy analysers

More and more non-linear consumers and plant components are finding their way into production facilities. They influence, for example, mains frequency, phase shift and amplitudes of the phases.

This has an influence on the quality of the electrical energy and thus on plant availability.

The energy analysers measure all quality parameters - from the parameters of symmetry to transients - and many more.

After comprehensive testing, optimisation steps can then be initiated to maximise the efficiency and availability of the plants.

### General ordering data

Order No.	2602580000
Type	<a href="#">ENERGY ANALYSER 550-24</a>
GTIN (EAN)	4050118655841
Qty.	1 items

## ENERGY ANALYSER 550-24

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

Depth	81 mm	Depth (inches)	3.189 inch
Height	144 mm	Height (inches)	5.6693 inch
Width	144 mm	Width (inches)	5.6693 inch
Net weight	1080 g		

## Temperatures

Storage temperature	-25 °C...70 °C	Operating temperature	-10 °C...55 °C
Humidity	5...95 %, no condensation		

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Measuring current input

Housing main material	Polycarbonate PC, Metal	Rated current	1 / 5 A
Current-measuring channels	4 + 2	Measuring accuracy for current	0.2 %
Residual current measuring	Yes	Harmonics, per order / current	1.-63.
Distortion factor THD-I in %	Yes	Max. current	5000 A

## Measuring voltage input

Low voltage network	3 phase 4 wire (L1 + L2 + L3 + N), 3 phase 3 wire (L1 + L2 + L3)	Measuring accuracy for voltage	0.1 %
Three-wire system	Yes	Quadrants	4
Harmonics, per order / voltage	1.-63.	Distortion factor THD-U in %	Yes
Measurement range, voltage L-L, AC	720 V	Measurement range, voltage L-N, AC	417 V
Four-wire system	Yes		

## Communication

Interface	RS485: 9.6 – 921.6 kbps, Profibus DP, Ethernet, Web server/e-mail	Protocol	Modbus RTU, Modbus-Gateway, Modbus TCP/IP, Modbus RTU over Ethernet, SNMP, BACnet (optional)
-----------	---	----------	--

## Inputs/outputs

Number of digital inputs	2	Number of digital outputs	2
Number of pulse outputs	2	Temperature input	Yes

## ENERGY ANALYSER 550-24

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Measurement data recording

Memory; minimum and maximum values	Yes	Memory size	256 MB
Number of memory values	10000 k	Update interval register	200 ms
Min. memory recording interval	1.00 s	Software	ecoExplorer go®
Integrated logic	Yes		

## Technical data

Version	Power measurement/ display for 1-, 3-phase mains	Type of mounting	Frontpanel mounting
Protection degree	IP40, IP20	Rated current	1 / 5 A
Max. current	5000 A	Display monitoring (monitor)	LCD
Standards	DIN EN 61326-1, DIN EN 61000-4-2, DIN EN 61000-4-3, DIN EN 61000-4-4, DIN EN 61000-4-5, DIN EN 61000-4-6, EN 61000-4-11, EN 55011, IEC 61010-1, IEC 61010-2-030, DIN EN 61000-4-8	Measurement range, voltage L-N, AC	417 V
Measurement range, voltage L-L, AC	720 V	Surge voltage category	600 V CAT III
Supply voltage	48...110 V AC, 24...150 V DC	Three-wire system	Yes
Four-wire system	Yes	Quadrants	4
Sampling frequency 50/60 Hz	20 kHz	Continuous measurements	Yes
Measurement result per second	5 ms	Effective value from the period (50/60 Hz)	10 / 12
Residual current measuring	Yes	Current-measuring channels	4 + 2
Measuring accuracy for voltage	0.1 %	Measuring accuracy for current	0.2 %
Measurement accuracy for active energy (kWh, .../5 A)	Class 0.2S	Operating-hours counter	Yes
Weekly time switch	Yes	Clock	Yes
Bimetal function	Yes		

## Voltage quality measurement

Harmonics, per order / voltage	1.-63.	Harmonics, per order / current	1.-63.
Distortion factor THD-U in %	Yes	Distortion factor THD-I in %	Yes
Unbalanced	Yes	Positive, negative and zero system	Yes
Brief interruptions	Yes	Sequence-of-events recorder function	Yes

## Insulation coordination

Surge voltage category	600 V CAT III
------------------------	---------------

## Classifications



ETIM 8.0	EC002301	ETIM 9.0	EC002301
ETIM 10.0	EC002301	ECLASS 14.0	27-14-23-30
ECLASS 15.0	27-14-23-30		

**ENERGY ANALYSER 550-24**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)



## ENERGY ANALYSER 550-24

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

## Accessories

[www.weidmueller.com](http://www.weidmueller.com)

### Accessories



### General ordering data

Type	ENERGY METER BRACKET B1	Version	
Order No.	<a href="#">2433040000</a>		
GTIN (EAN)	4050118446364		
Qty.	1 ST		
Type	ENERGY METER SEAL L144	Version	
Order No.	<a href="#">2495630000</a>		
GTIN (EAN)	4050118505870		
Qty.	1 ST		