

**WPD 113 1X185+1X150/8X35 GY**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Our WPD 1XX distribution blocks are used in all situations where power is supplied and distributed. Their user-friendly design creates a better overview and enables Rapid, efficient implementation of space-saving power distribution.

**General ordering data**

Version	Potential distributor terminal, Screw connection, Light Grey, 185 mm <sup>2</sup> , 353 A, 1000 V, Number of connections: 10, Number of levels: 1
Order No.	<a href="#">2603740000</a>
Type	WPD 113 1X185+1X150/8X35 GY
GTIN (EAN)	4050118681420
Qty.	1 items

## WPD 113 1X185+1X150/8X35 GY

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (cURus)	E60693
Certificate no. (cULus)	E511333

### Dimensions and weights

Depth	80.3 mm	Depth (inches)	3.1614 inch
Height	126.3 mm	Height (inches)	4.9724 inch
Width	62.6 mm	Width (inches)	2.4646 inch
Net weight	740 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...85 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	130 °C

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	9b5f0838-1f0b-4c14-9fc7-3f5e6ee75be2

### Material data

Basic material	Wemid	Colour	Light Grey
UL 94 flammability rating	V-0		

### System specifications

Version	Screw connection	End cover plate required	No
Number of potentials	1	Number of levels	1
Number of clamping points per level	10	Levels cross-connected internally	No
Mounting rail	TS 35, Mounting plate	N-function	No
PE function	No	PEN function	No

### Additional technical data

Open sides	closed	Snap-on	Yes
Installation advice	Terminal rail / mounting plate	Explosion-tested version	Yes
Type of mounting	Snap-on, Direct mounting		

### Conductors for clamping (additional connection)

Connection type, additional connection	Screw connection
--	------------------

**WPD 113 1X185+1X150/8X35 GY**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**
**Conductors for clamping (rated connection)**

Wire connection cross section AWG, max.	kcmil 300	Connection direction	on side
Type of connection 2	Screw connection	Type of connection	Screw connection
Number of connections	10	Clamping range, max.	185 mm <sup>2</sup>
Clamping range, min.	1.5 mm <sup>2</sup>	Wire connection cross section AWG, min.	AWG 12
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	1.5 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	150 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	1.5 mm <sup>2</sup>	Wire connection cross section, finely stranded, max.	0 mm <sup>2</sup>
Wire connection cross section, finely stranded, min.	1.5 mm <sup>2</sup>	Connection cross-section, stranded, max.	185 mm <sup>2</sup>
Connection cross-section, stranded, min.	1.5 mm <sup>2</sup>	Wire connection cross-section, solid core, max.	185 mm <sup>2</sup>
Wire connection cross-section, solid core, min.	1.5 mm <sup>2</sup>		

**General**

Number of poles	1	Wire connection cross section AWG, max.	kcmil 300
Installation advice	Terminal rail / mounting plate	Wire connection cross section AWG, min.	AWG 12
Standards	IEC 60947-7-1	Mounting rail	TS 35, Mounting plate

**Rating data**

Rated cross-section	185 mm <sup>2</sup>	Rated voltage	1000 V
Rated AC voltage	1000 V	Rated DC voltage	1500 V
Nominal current	353 A	Current at maximum wires	353 A
Standards	IEC 60947-7-1	Rated impulse withstand voltage	8 kV
Surge voltage category	III	Pollution severity	3

**UL rating data**

Certificate No. (cURus)	E60693
-------------------------	--------

**Important note**

Product information	The socket complies with flammability class V-2 according to UL94.
---------------------	--

**Classifications**

ETIM 8.0	EC000897	ETIM 9.0	EC000897
ETIM 10.0	EC000897	ECLASS 14.0	27-25-01-19
ECLASS 15.0	27-25-01-19		

WPD 113 1X185+1X150/8X35 GY

Weidmüller Interface GmbH & Co. KG  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

Drawings

www.weidmueller.com



Conductor connection data according to IEC 60947-1 (Cu)

Input	connection point A		connection point B		Output	connection point 1-8	
	Copper	Aluminum	Copper	Aluminum		Copper	Aluminum
185 mm²	25 Nm		25 Nm		35 mm²	6 Nm	6 Nm
150 mm²			25 Nm		25 mm²		
120 mm²			25 Nm		16 mm²		
95 mm²			25 Nm		10 mm²		
70 mm²			25 Nm		6 mm²		
50 mm²			25 Nm		4 mm²		
Strapping lengths	23 mm		20 mm		2.5 mm²		
Allen screw	M10		M10		16 mm		
					Alloy screw		


 Stranded  
 Solid  
 Flexible with ferrule



Conductor connection data according to UL 1059 (Al+Cu)

Input (line)	connection point A		connection point B			
	Copper	Aluminum	Copper	Aluminum	Copper	Aluminum
350 kcmil						
300 kcmil						
250 kcmil	249.8 lb in.		398.3 lb in.			
200 kcmil	249.8 lb in.		398.3 lb in.	249.8 lb in.	398.3 lb in.	398.3 lb in.
150 kcmil						
100 kcmil						
75 kcmil						
50 kcmil						
max. current	310 A	285 A	250 A	230 A	285 A	255 A
Voltage max. B.C. (UR)	1000 V		1000 V			

Output	connection point 1/2/3/4/5/6/7/8	
	Copper	Aluminum
JWS 2		
JWS 3		
JWS 4		
JWS 5	124.8 lb in.	124.8 lb in.
JWS 6	124.8 lb in.	124.8 lb in.
JWS 10		
JWS 12		
max. current	115 A	90 A
Voltage max. B.C. (UR)	1000 V	



 Stranded  
 Solid  
 Flexible with ferrule

