



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

### General ordering data

Version	cable lug, terminal end,400 mm <sup>2</sup> ,400 mm <sup>2</sup> - 400 mm <sup>2</sup>
Order No.	<a href="#">2578040000</a>
Type	KRN-M16/-400
GTIN (EAN)	4064675018131
Qty.	15 items

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Net weight	203.45 g
------------	----------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Connectors**

Conductor cross-section, max.	400 mm <sup>2</sup>	Conductor cross-section, min.	400 mm <sup>2</sup>
Conductor cross-section	400 mm <sup>2</sup>	Insulation	not available
Hole	M 16	Identification colour	None
Inside diameter of shaft (d1)	27.5 mm	Outside diameter of shaft (d3)	33.5 mm
Shaft length (a)	47 mm	Connection length (l)	92 mm
Inside diameter of flange (d2)	17 mm	Flange width (b)	49 mm

**Classifications**

ETIM 8.0	EC001051	ETIM 9.0	EC001051
ETIM 10.0	EC001051	ECLASS 14.0	27-40-02-05
ECLASS 15.0	27-40-02-05		

Drawings

