

SQV 6/2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

Version	Cross-connector (terminal), when screwed in, black, grey, 125 A, Number of poles: 2, Pitch in mm (P): 18.00, Insulated: No, Width: 26 mm
Order No.	2615080000
Type	SQV 6/2
GTIN (EAN)	4050118653908
Qty.	100 items

SQV 6/2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	32 mm	Depth (inches)	1.2598 inch
Height	7.5 mm	Height (inches)	0.2953 inch
Width	26 mm	Width (inches)	1.0236 inch
Net weight	8.71 g		

Temperatures

Storage temperature -25 °C...55 °C Ambient temperature -5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
REACH SVHC No SVHC above 0.1 wt%

Material data

Basic material PA Colour black, grey

System specifications

Version Cross-connector

Additional technical data

Type of fixing when screwed in Explosion-tested version No
Type of mounting when screwed in

Dimensions

Pitch in mm (P) 18.00 mm

General

Number of poles 2

Rating data

Rated voltage 400 V Nominal current 125 A

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		