

SQV 6/3

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

| | |
|------------|--|
| Version | Cross-connector (terminal), when screwed in, black, grey, 125 A, Number of poles: 3, Pitch in mm (P): 18.00, Insulated: No, Width: 43.1 mm |
| Order No. | 2615090000 |
| Type | SQV 6/3 |
| GTIN (EAN) | 4050118653892 |
| Qty. | 50 items |

SQV 6/3

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| RoHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 32 mm | Depth (inches) | 1.2598 inch |
| Height | 7.5 mm | Height (inches) | 0.2953 inch |
| Width | 43.1 mm | Width (inches) | 1.6968 inch |
| Net weight | 12.69 g | | |

Temperatures

| | | | |
|---------------------|----------------|---------------------|---------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -5 °C...40 °C |
|---------------------|----------------|---------------------|---------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|----------------|----|--------|-------------|
| Basic material | PA | Colour | black, grey |
|----------------|----|--------|-------------|

System specifications

| | |
|---------|-----------------|
| Version | Cross-connector |
|---------|-----------------|

Additional technical data

| | | | |
|------------------|-----------------|--------------------------|----|
| Type of fixing | when screwed in | Explosion-tested version | No |
| Type of mounting | when screwed in | | |

Dimensions

| | |
|-----------------|----------|
| Pitch in mm (P) | 18.00 mm |
|-----------------|----------|

General

| | |
|-----------------|---|
| Number of poles | 3 |
|-----------------|---|

Rating data

| | | | |
|---------------|-------|-----------------|-------|
| Rated voltage | 400 V | Nominal current | 125 A |
|---------------|-------|-----------------|-------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000489 | ETIM 9.0 | EC000489 |
| ETIM 10.0 | EC000489 | ECLASS 14.0 | 27-25-03-03 |
| ECLASS 15.0 | 27-25-03-03 | | |