Data sheet

SAI-T-M12-K

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration



RoHS COMPLIANT

General ordering data

Version	Y connector
Order No.	2616500000
Type	SAI-T-M12-K
GTIN (EAN)	4050118621563
Qty.	1 items

Data sheet

SAI-T-M12-K

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	
ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E310075

Dimensions and weights

Net weight	100 g

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4

Connection data

Group outlet - plug-in connector	M12 pin	Single outlet 1 - plug-in connector	M12 socket
Single outlet 2 - plug-in connector	M12 socket	Tightening torque	M12: 0.8 - 1.2 Nm

Technical data customisable plug-in connectors

Number of poles	5	Coding	K-coded
Contact surface	Gold-plated	Housing main material	TPU
Nominal current	12 A	Protection degree	IP65, IP67, IP68
Pollution severity	3	Cable gland	M 12
Shield connection	No	Temperature range of housing	-30...+90 °C

Standards

Connector standard	IEC 61076-2-111

General data

Number of poles	5	Coding	K-coded
Contact surface	Gold-plated	Housing main material	TPU
Nominal current	12 A	Protection degree	IP65, IP67, IP68
Pollution severity	3	Cable gland	M 12
Rated voltage	630 V AC	Shield connection	No
Temperature range of housing	-30...+90 °C	Conductor O.D.	-

Classifications

ETIM 8.0	EC002925	ETIM 9.0	EC002925
ETIM 10.0	EC002925	ECLASS 14.0	27-44-01-06
ECLASS 15.0	27-44-01-06		


SAI-T-M12-K

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings


Dimensioned drawing



Pole scheme



Pole scheme



Pole scheme

