

THM WO 14/22 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 1.9 - 5 mm, 14 x 22 mm, white
Order No.	2621530000
Type	THM WO 14/22 WS
GTIN (EAN)	4050118625516
Qty.	5000 items

THM WO 14/22 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.03 mm	Depth (inches)	0.001 inch
Height	14 mm	Height (inches)	0.5512 inch
Width	22 mm	Width (inches)	0.8661 inch
Net weight	0.05 g		

Temperatures

Operating temperature range	-40...
-----------------------------	--------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Type of printing	neutral	
Version	Self-adhesive	
Width	22 mm	
UL 94 flammability rating	V-0	
Operating temperature range, min.	-40 °C	
Colour	white	
Halogen	No	
Printed characters	without	
Number of markers per packaging unit	Form of supply	Label reel
Size of labelling field	6 x 14 mm	
compatible printer	THM MULTIMARK , THM MULTIMARK PLUS	
Number of markers per combination	1 Label reel = Conductor and cable markers	
Operating temperature range	-40...	
Number per roll	5000	

Conductor and cable markers

Halogen	No	Conductor O.D., max.	5 mm
Conductor O.D., min.	1.9 mm	Conductor O.D.	1.9 - 5 mm

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

