


SFX-DT 11/60 MC SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



We support our customers in the food industry with detectable marking solutions to ensure the high standards required within the framework of the HACCP concept. Thanks to a metallic filler, our detectable MultiCards can be reliably identified by metal and X-ray detectors. This minimises the risk of product contamination in the production process. Maximum safety is ensured with important product properties, such as corrosion resistance or higher ageing resistance to UV radiation in indoor areas and heat. These properties are regularly tested and confirmed in our own accredited laboratory.

Not suitable for direct food contact.

- Detectable by metal and X-ray detectors
- Visually recognisable by blue colour
- Corrosion resistant metallic filler
- Clear and resistant print image
- Available in different versions for a wide variety of marking requirements

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|------------|--|
| Version | Conductor and cable markers, 7 - 40 mm, 60 x 11 mm, blue |
| Order No. | 2622430000 |
| Type | SFX-DT 11/60 MC SDR |
| GTIN (EAN) | 4050118623451 |
| Qty. | 12 items |

SFX-DT 11/60 MC SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| RoHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 0.8 mm | Depth (inches) | 0.0315 inch |
| Height | 60 mm | Height (inches) | 2.3622 inch |
| Width | 11 mm | Width (inches) | 0.4331 inch |
| Net weight | 1.83 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

Environmental Product Compliance

| | |
|--------------------------|---------------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |
| Product Carbon Footprint | Cradle to gate 0.020 kg CO2 eq. |

General data

| | | | | | |
|---|---|-----------|--|--|--|
| Version | Installation with cable ties | | | | |
| Width | 11 mm | | | | |
| UL 94 flammability rating | HB | | | | |
| Operating temperature range, max. | 100 °C | | | | |
| Operating temperature range, min. | -40 °C | | | | |
| Colour | blue | | | | |
| Halogen | No | | | | |
| Basic material | Polyamide 66 | | | | |
| Printed characters | To customer specification | | | | |
| Number of markers per packaging unit | Form of supply | MultiCard | | | |
| Size of labelling field | 44 x 11 mm | | | | |
| Detectable in accordance with Rondotest | 4.7 mm Al | | | | |
| Recommended industries | Food processing industry | | | | |
| compatible printer | PRINTJET CONNECT , MCP BASIC 2 , MCP PLUS 2 | | | | |
| Number of markers per combination | 1 MultiCard = Conductor and cable markers | | | | |
| Operating temperature range | -40...100 °C | | | | |

Conductor and cable markers

| | | | |
|----------------------------------|--------------------------|-------------------------------|---------------------|
| Halogen | No | Conductor cross-section, max. | 500 mm ² |
| Conductor cross-section, min. | 16 mm ² | Conductor O.D., max. | 40 mm |
| Conductor O.D., min. | 7 mm | Conductor O.D. | 7 - 40 mm |
| Cross-section for connected wire | 16 - 500 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

SFX-DT 11/60 MC SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

