


SFX-DT 9/24 MC SDR

Weidmüller Interface GmbH & Co. KG

Klingenbergsstraße 26
D-32758 Detmold
Germanywww.weidmueller.com

We support our customers in the food industry with detectable marking solutions to ensure the high standards required within the framework of the HACCP concept. Thanks to a metallic filler, our detectable MultiCards can be reliably identified by metal and X-ray detectors. This minimises the risk of product contamination in the production process. Maximum safety is ensured with important product properties, such as corrosion resistance or higher ageing resistance to UV radiation in indoor areas and heat. These properties are regularly tested and confirmed in our own accredited laboratory.

Not suitable for direct food contact.

- Detectable by metal and X-ray detectors
- Visually recognisable by blue colour
- Corrosion resistant metallic filler
- Clear and resistant print image
- Available in different versions for a wide variety of marking requirements

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	Conductor and cable markers, 7 - 40 mm, 24 x 15 mm, blue
Order No.	2622440000
Type	SFX-DT 9/24 MC SDR
GTIN (EAN)	4050118623468
Qty.	32 items

SFX-DT 9/24 MC SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

RoHS	Conform
------	---------

Dimensions and weights

Depth	0.8 mm	Depth (inches)	0.0315 inch
Height	24 mm	Height (inches)	0.9449 inch
Width	15 mm	Width (inches)	0.5906 inch
Net weight	0.71 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%
Product Carbon Footprint	Cradle to gate 0.007 kg CO2 eq.

General data

Version	Installation with cable ties				
Width	15 mm				
UL 94 flammability rating	HB				
Operating temperature range, max.	100 °C				
Operating temperature range, min.	-40 °C				
Colour	blue				
Halogen	No				
Basic material	Polyamide 66				
Printed characters	To customer specification				
Number of markers per packaging unit	Form of supply	MultiCard			
Size of labelling field	23.9 x 9 mm				
Detectable in accordance with Rondotest	4.7 mm Al				
Recommended industries	Food processing industry				
compatible printer	PRINTJET CONNECT , MCP BASIC 2 , MCP PLUS 2				
Number of markers per combination	1 MultiCard = Conductor and cable markers				
Operating temperature range	-40...100 °C				

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	500 mm ²
Conductor cross-section, min.	16 mm ²	Conductor O.D., max.	40 mm
Conductor O.D., min.	7 mm	Conductor O.D.	7 - 40 mm
Cross-section for connected wire	16 - 500 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

SFX-DT 9/24 MC SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

