


**A2T 2.5 3C N-PE****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

To feed through power, signal, and data is the classical requirement in electrical engineering and panel building. The insulating material, the connection system and the design of the terminal blocks are the differentiating features. A feed-through terminal block is suitable for joining and/or connecting one or more conductors. They could have one or more connection levels that are on the same potential or insulated against one another.

**General ordering data**

Version	Feed-through terminal, Double-tier terminal, PUSH IN, 2.5 mm <sup>2</sup> , 800 V, 22 A, dark beige
Order No.	<a href="#">2623550000</a>
Type	A2T 2.5 3C N-PE
GTIN (EAN)	4050118626513
Qty.	50 items

## A2T 2.5 3C N-PE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (cURusEX)	E184763

### Dimensions and weights

Depth	64 mm	Depth (inches)	2.5197 inch
Depth including DIN rail	38.4 mm	Height	114.5 mm
Height (inches)	4.5079 inch	Width	5.1 mm
Width (inches)	0.2008 inch	Net weight	21.95 g

### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Basic material	Wemid	Colour	dark beige
Colour of operational elements	orange	UL 94 flammability rating	V-0

### Rating data IECEX/ATEX

Certificate No. (ATEX)	TUEV16ATEX7909U	Certificate No. (IECEX)	IECEXTUR16.0036U
Max. voltage (ATEX)	550 V	Current (ATEX)	20 A
Wire cross section max. (ATEX)	2.5 mm <sup>2</sup>	Max. voltage (IECEX)	550 V
Current (IECEX)	20 A	Wire cross section max. (IECEX)	2.5 mm <sup>2</sup>

### System specifications

End cover plate required	Yes	Number of potentials	2
Number of levels	2	Number of clamping points per level	3
Levels cross-connected internally	No	PE connection	Yes
Mounting rail	TS 35	N-function	Yes
PE function	Yes	PEN function	No

### Additional technical data

With snap-in pegs	No	Open sides	right
Snap-on	No	Type of fixing	Snap-on

## A2T 2.5 3C N-PE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

### Technical data

Installation advice	Rail	Explosion-tested version	Yes
Type of mounting	TS 35		

#### Conductors for clamping (additional connection)

Connection type, additional connection PUSH IN

#### Conductors for clamping (rated connection)

Gauge to IEC 60947-1	A3	
Wire connection cross section AWG, max.	AWG 12	
Connection direction	top	
Stripping length	10 mm	
Type of connection 2	PUSH IN	
Type of connection	PUSH IN	
Number of connections	6	
Clamping range, max.	4 mm <sup>2</sup>	
Clamping range, min.	0.14 mm <sup>2</sup>	
Blade size	0.6 x 3.5 mm	
Wire connection cross section AWG, min.	AWG 28	
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max.	2.5 mm <sup>2</sup>	
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	0.14 mm <sup>2</sup>	
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	4 mm <sup>2</sup>	
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.14 mm <sup>2</sup>	
Wire connection cross section, finely stranded, max.	4 mm <sup>2</sup>	
Wire connection cross section, finely stranded, min.	0.14 mm <sup>2</sup>	
Connection cross-section, stranded, max.	4 mm <sup>2</sup>	
Connection cross-section, stranded, min.	0.14 mm <sup>2</sup>	
Twin wire-end ferrules, max.	0.75 mm <sup>2</sup>	
Twin wire-end ferrules, min.	0.5 mm <sup>2</sup>	
Wire connection cross-section, solid core, max.	2.5 mm <sup>2</sup>	
Wire connection cross-section, solid core, min.	0.14 mm <sup>2</sup>	
Connection cross-section, finely stranded, min.	0.14 mm <sup>2</sup>	
Tube length for wire-end ferrule with plastic collar DIN 46228/4	Tube length	min. 6 mm
		max. 8 mm
	Cross-section for conductor connection	min. 0.14 mm <sup>2</sup>
		max. 0.34 mm <sup>2</sup>
	Tube length	min. 6 mm
		max. 12 mm
	Cross-section for conductor connection	min. 0.5 mm <sup>2</sup>
		max. 1 mm <sup>2</sup>
	Tube length	min. 8 mm
		max. 12 mm
	Cross-section for conductor connection	min. 1.5 mm <sup>2</sup>

## A2T 2.5 3C N-PE

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

Tube length for twin wire-end ferrule	Tube length	max.	2.5 mm <sup>2</sup>
		min.	8 mm
	Cross-section for conductor connection	max.	12 mm
		min.	0.5 mm <sup>2</sup>
Tube length for wire-end ferrule without plastic collar DIN 46228/1	Tube length	nominal	5 mm
		max.	0.75 mm <sup>2</sup>
	Cross-section for conductor connection	min.	6 mm
		max.	10 mm
	Cross-section for conductor connection	min.	0.5 mm <sup>2</sup>
		max.	1 mm <sup>2</sup>
	Tube length	min.	7 mm
		max.	12 mm
	Cross-section for conductor connection	min.	1.5 mm <sup>2</sup>
		max.	4 mm <sup>2</sup>

### General

Wire connection cross section AWG, max.	AWG 12	Installation advice	Rail
Wire connection cross section AWG, min.	AWG 28	Standards	IEC 60947-7-1
Mounting rail	TS 35		

### Rating data

Rated cross-section	2.5 mm <sup>2</sup>	Rated voltage	800 V
Rated DC voltage	800 V	Nominal current	22 A
Current at maximum wires	22 A	Standards	IEC 60947-7-1
Volume resistance according to IEC 60947-7-x	1.33 mΩ	Rated impulse withstand voltage	8 kV
Power loss in accordance with IEC 60947-7-x	0.77 W	Surge voltage category	III
Pollution severity	3		

### Classifications

ETIM 8.0	EC000897	ETIM 9.0	EC000897
ETIM 10.0	EC000897	ECLASS 14.0	27-25-01-02
ECLASS 15.0	27-25-01-02		

Drawings

