


## VCG 24V EX 2 G 1/2

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



VARITECTOR Cable Gland (VCG) protects intrinsically safe circuits in IP67 applications

- Tested in accordance with IEC/EN 61643-21
- Suitable for use in EX areas
- High protection class with IP67
- Screw-in housing with different threads
- HART-compatible

### General ordering data

Order No.	2593160000
Type	<a href="#">VCG 24V EX 2 G 1/2</a>
GTIN (EAN)	4050118605143
Qty.	1 items

## VCG 24V EX 2 G 1/2

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

Height	24 mm	Height (inches)	0.9449 inch
Height of lowest version	54 mm	Width	24 mm
Width (inches)	0.9449 inch	Length	78 mm
Length (inches)	3.0709 inch	Diameter	28 mm
Net weight	180 g		

### Temperatures

Storage temperature -30 °C...60 °C      Operating temperature -30 °C...60 °C

### Environmental Product Compliance

RoHS Compliance Status Compliant  
 REACH SVHC No SVHC above 0.1 wt%

### Protection Ex - Data

ATEX - dust labelling	IEC Ex BAS 18.0085X, Ex ia IIIC T85 °C Da, (-30 °C≤Ta≤50 °C)	ATEX - gas labelling	18ATEX0141X, II 1GD, Ex ia II T6 Ga, (-30 °C≤Ta≤50 °C)
Input power, max. PI	2 W	Input voltage, max. Ui	50 V
Input current, max. Ii	0.8 A	Internal capacity, max. Ci	0 nF
Internal inductance, max. Li	60 µH		

### General data

Segment	Measurement - Monitoring - Setting	Version	Stainless steel screw mounting housing
Design	straight, G 1/2 (BSP 1/2)	Colour	silver
Protection degree	IP67	FIELD BUS FOUNDATION BUS H1 compatible	According to IEC 61158-2

### Rated data IEC / EN

Rated voltage (DC), max.	33 V	Rated voltage (DC)	24 V
Response time / fallback time	< 1 ns	Frequency range, min.	0 Hz
Standards	IEC 61643-21, IEC 60079-0, IEC 60079-11	Dielectric strength at FG against PE	≥ 500 V
Requirements category acc. to IEC 61643-21	D1, C1, C2, C3	Insertion loss	30 MHz
Lightning test current, limp (10/350 µs) wire-wire	1 kA	Lightning test current, limp (10/350 µs) Wire-PE	1 kA
Discharge current In (8/20µs) wire-wire	5 kA	Discharge current Imax (8/20µs) wire-PE	10 kA
Discharge current Imax (8/20µs) wire-wire	10 kA	Input voltage, max. Ui	50 V

## VCG 24V EX 2 G 1/2

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Connection data

Cross-section	1 mm <sup>2</sup>	Wire connection method	Cable length: 250 mm (min.)
---------------	-------------------	------------------------	-----------------------------

### General data

Protection degree	IP67	Colour	silver
-------------------	------	--------	--------

### Ratings IECEx/ATEX/cUL

ATEX - dust labelling	IEC Ex BAS 18.0085X, Ex ia IIIC T85 °C Da, (-30 °C ≤ Ta ≤ 50 °C)	ATEX - gas labelling	18ATEX0141X, II 1GD, Ex ia II T6 Ga, (-30 °C ≤ Ta ≤ 50 °C)
Marking EN 60079	Ex ec nC IIC T4 Gc		

### Guarantee

Time interval	5 years
---------------	---------

### Classifications


ETIM 8.0	EC000943	ETIM 9.0	EC000943
ETIM 10.0	EC000943	ECLASS 14.0	27-17-15-02
ECLASS 15.0	27-17-15-02		

VCG 24V EX 2 G 1/2

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

Drawings

www.weidmueller.com



Similar to illustration