

## D-SUB F6.1 T09VB 3.2B2 TY BK

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)



The product range encompasses the following designs:

- 90°, lying (horizontal) and 180°, standing (vertical)
- Flange design as drilled hole, UNC 4-40 threaded nut and UNC 4-40 threaded bolt
- Stamped contacts (Rated current: 3 A)
- THT soldering process
- Wide range of different design types, also with snap-on clip
- Packed in tray (TY)
- Extended temperature range of -55 °C to +85 °C for maximum performance
- Design in accordance with IEC 60807-3 (IEC 807-3) and DIN 41652

### General ordering data

Version	OMNIMATE Data - D-SUB connector, female header, Thread-bolt UNC 4-40, Snap-on clip, THT solder connection, Pitch in mm (P): 2.77 mm, Number of poles: 9, 500, PBT glass fibre reinforced UL 94 V-0, black, Tray (manual assembly)
Order No.	<a href="#">2626670000</a>
Type	D-SUB F6.1 T09VB 3.2B2 TY BK
GTIN (EAN)	4050118663617
Qty.	90 items
Packaging	Tray (manual assembly)
Delivery status	This article will no longer be available in the future.
Available until	2024-08-31T00:00:00+02:00

Creation date 03.03.2026 02:50:44 MEZ

Catalogue status / Drawings

**D-SUB F6.1 T09VB 3.2B2 TY BK**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data****Approvals**

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (UR)	E92202

**Dimensions and weights**

Depth	12.55 mm	Depth (inches)	0.4941 inch
Width	30.81 mm	Width (inches)	1.213 inch
Net weight	7.67 g		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**System specifications**

Number of poles	9
Solder pin length (l)	4.6 mm
Mounting onto the PCB	THT solder connection
Pitch in inches (P)	0.109 "
Shielding material	Steel
Side termination, characteristic	Thread-bolt UNC 4-40, Snap-on clip
Type of connection	Solder connection
Solder eyelet hole diameter (D)	1.1 mm
Product family	OMNIMATE Data - D-SUB connector
Pitch in mm (P)	2.77 mm
Protection degree	IP20
Plugging cycles	500
Model	Socket connector
Outgoing elbow	180°
Shield surface	tinned
Soldering process	Manual soldering, Wave soldering
Solder pin dimensions	Octagonal
Solder pin length tolerance	Lower tolerance with prefix (reveals minimum) -0,25
	Upper tolerance with prefix (reveals maximum) +0,25
	Tolerance, unit mm
Solder pin length tolerance	+0,25 / -0,25 mm
Tolerance of solder pin position	± 0.1 mm

**Electrical properties**

Dielectric strength, contact / contact	1000 V AC	Volume resistance	≤20 mΩ
Nominal voltage	250 V	Rated current	3 A

**Material data**

Insulating material	PBT glass fibre reinforced UL 94 V-0	Colour	black
Colour chart (similar)	RAL 9011	Moisture Level (MSL)	

## D-SUB F6.1 T09VB 3.2B2 TY BK

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Technical data

UL 94 flammability rating	V-0	Contact base material	Copper alloy
Contact material	Cu-alloy	Contact surface	Gold over nickel
Layer structure of plug contact	$\geq 50 \mu\text{m Ni} / \geq 1 \mu\text{m Au}$	Storage temperature, min.	-55 °C
Storage temperature, max.	85 °C	Operating temperature, min.	-55 °C
Operating temperature, max.	105 °C		

### Packing

Packaging	Tray (manual assembly)	VPE length	304.00 mm
VPE width	253.00 mm	VPE height	16.00 mm

### Important note

Notes

### Classifications

ETIM 8.0	EC002637	ETIM 9.0	EC002637
ETIM 10.0	EC002637	ECLASS 14.0	27-46-02-01
ECLASS 15.0	27-46-02-01		

**D-SUB F6.1 T09VB 3.2B2 TY BK**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

**Product image**



**D-SUB F6.1 T09VB 3.2B2 TY BK**


**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

Drawings

Packaging drawing

Scale	Free
TOLERANCE	
X.	±0.38
X.X	±0.25
X.XX	±0.13
DIM	TOL
X.°	±3°
X.X°	±1.0°
Angle	TOL



Dimensional drawing

**RECOMMENDED PCB LAYOUT**

POSITIONS	A±0.15	B±0.10	D±0.13	E±0.08	F±0.10
9	30.81	24.99	16.33	11.08	19.20
15	39.20	33.30	24.70	19.39	27.70
25	53.05	47.04	38.40	33.24	41.10

#4-40 unc screwlock installed