

## WPD 111 1X95/4X35 BL

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Our WPD 1XX distribution blocks are used in all situations where power is supplied and distributed. Their user-friendly design creates a better overview and enables Rapid, efficient implementation of space-saving power distribution.

### General ordering data

Version	Potential distributor terminal, Screw connection, blue, 95 mm <sup>2</sup> , 232 A, 1000 V, Number of connections: 5, Number of levels: 1
Order No.	<a href="#">2603800000</a>
Type	WPD 111 1X95/4X35 BL
GTIN (EAN)	4050118681277
Qty.	1 items

## WPD 111 1X95/4X35 BL

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (cURus)	E60693
Certificate no. (cULus)	E511333

### Dimensions and weights

Depth	69.4 mm	Depth (inches)	2.7323 inch
Height	105 mm	Height (inches)	4.1338 inch
Width	36.6 mm	Width (inches)	1.4409 inch
Net weight	240 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...85 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	130 °C

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	9b5f0838-1f0b-4c14-9fc7-3f5e6ee75be2

### Material data

Basic material	Wemid	Colour	blue
UL 94 flammability rating	V-0		

### System specifications

Version	Screw connection	End cover plate required	No
Number of potentials	1	Number of levels	1
Number of clamping points per level	5	Levels cross-connected internally	No
Mounting rail	TS 35, Mounting plate	N-function	No
PE function	No	PEN function	No

### Additional technical data

Open sides	closed	Snap-on	Yes
Installation advice	Terminal rail / mounting plate	Explosion-tested version	Yes
Type of mounting	Snap-on, Direct mounting		

### Conductors for clamping (additional connection)

Connection type, additional connection	Screw connection
--	------------------

## WPD 111 1X95/4X35 BL

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Conductors for clamping (rated connection)

Wire connection cross section AWG, max.	AWG 4/0	Connection direction	on side
Type of connection 2	Screw connection	Type of connection	Screw connection
Number of connections	5	Clamping range, max.	95 mm <sup>2</sup>
Clamping range, min.	2.5 mm <sup>2</sup>	Wire connection cross section AWG, min.	AWG 12
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	2.5 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	70 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	2.5 mm <sup>2</sup>	Wire connection cross section, finely stranded, max.	0 mm <sup>2</sup>
Wire connection cross section, finely stranded, min.	2.5 mm <sup>2</sup>	Connection cross-section, stranded, max.	95 mm <sup>2</sup>
Connection cross-section, stranded, min.	2.5 mm <sup>2</sup>	Wire connection cross-section, solid core, max.	95 mm <sup>2</sup>
Wire connection cross-section, solid core, min.	2.5 mm <sup>2</sup>		

## General

Number of poles	1	Wire connection cross section AWG, max.	AWG 4/0
Installation advice	Terminal rail / mounting plate	Wire connection cross section AWG, min.	AWG 12
Standards	IEC 60947-7-1	Mounting rail	TS 35, Mounting plate

## Rating data

Rated cross-section	95 mm <sup>2</sup>	Rated voltage	1000 V
Rated AC voltage	1000 V	Rated DC voltage	1500 V
Nominal current	232 A	Current at maximum wires	232 A
Standards	IEC 60947-7-1	Rated impulse withstand voltage	8 kV
Surge voltage category	III	Pollution severity	3

## UL rating data

Certificate No. (cURus)	E60693
-------------------------	--------

## Important note

Product information	The socket complies with flammability class V-2 according to UL94.
---------------------	--

## Classifications

ETIM 8.0	EC000897	ETIM 9.0	EC000897
ETIM 10.0	EC000897	ECLASS 14.0	27-25-01-19
ECLASS 15.0	27-25-01-19		

WPD 111 1X95/4X35 BL

Weidmüller Interface GmbH & Co. KG  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

Drawings

www.weidmueller.com



Conductor connection data according to IEC 60947-1 (Cu)

connection point A		connection point A	
Input	Copper	Output	Copper
1x 95 mm <sup>2</sup>	14 Nm	1x 35 mm <sup>2</sup>	6 Nm
95 mm <sup>2</sup>	14 Nm	35 mm <sup>2</sup>	6 Nm
70 mm <sup>2</sup>		25 mm <sup>2</sup>	
50 mm <sup>2</sup>		18 mm <sup>2</sup>	
35 mm <sup>2</sup>		10 mm <sup>2</sup>	
25 mm <sup>2</sup>		6 mm <sup>2</sup>	
16 mm <sup>2</sup>		4 mm <sup>2</sup>	
10 mm <sup>2</sup>		2,5 mm <sup>2</sup>	
Stripping lengths	21 mm	Stripping lengths	10 mm
Allen screw	M12	Allen screw	M6



Conductor connection data according to 1059 (Al+Cu)

connection point A		connection point 1 / 2 / 3 / 4	
Input (line)	Copper	Aluminum	Aluminum
AWG 4/0			
AWG 3/0			
AWG 2/0	200 lb In.	200 lb In.	124.8 lb In.
AWG 1/0			
AWG 1			
AWG 2			
AWG 3			
AWG 4			
AWG 6			
AWG 8			
Max. current	230 A	200 A	180 A
Voltage size IEC 609	1000 V		

