

## SRQB 3/2

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

### General ordering data

Version	Cross-connector (terminal), when screwed in, black, 41 A, Number of poles: 2, Pitch in mm (P): 9.00, Insulated: Yes, Width: 14.1 mm
Order No.	<a href="#">2615190000</a>
Type	SRQB 3/2
GTIN (EAN)	4050118653694
Qty.	100 items

## SRQB 3/2

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS Conform

## Dimensions and weights

Depth	2.8 mm	Depth (inches)	0.1102 inch
Height	23 mm	Height (inches)	0.9055 inch
Width	14.1 mm	Width (inches)	0.5551 inch
Net weight	1.79 g		

## Temperatures

Storage temperature -25 °C...55 °C Ambient temperature -5 °C...40 °C

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption  
REACH SVHC No SVHC above 0.1 wt%

## Material data

Basic material PA Colour black  
UL 94 flammability rating V-2

## System specifications

Version Cross-connector

## Additional technical data

Type of fixing when screwed in Explosion-tested version No  
Type of mounting when screwed in

## Dimensions

Pitch in mm (P) 9.00 mm

## General

Number of poles 2

## Rating data

Rated voltage 400 V Nominal current 41 A

## Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		