

BVFL HYBRID CUSTOMER SAMPLE BOX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image



OMNIMATE Signal and OMNIMATE Power are PCB terminal blocks, plug-in connector and panel feedthrough terminal blocks for industrial applications with a focus on signal processing and power electronics.

Power for high currents up to 232 A and voltages up to 1000 V (IEC) or 230 A at 600 V (UL). The components are optimised for application-oriented design, efficient production and reliable application.

OMNIMATE Data are RJ45 and USB circuit board sockets for safe data transmission in the Industrial Ethernet environment.

RJ45 components from Weidmüller ensure reliable transmission with high data rates up to 1 Gbit/s. With different variants for THT, THR or SMT solder processes, the female sockets are suitable for all common techniques of PCB assembly. The different design types of the RJ45 circuit board sockets allow adaptation to the individual enclosure design.

General ordering data

Version	PCB plug-in connector, Sample kit, OMNIMATE Power - series BV/SV 7.62HP
Order No.	2615770000
Type	BVFL HYBRID CUSTOMER SAMPLE BOX
GTIN (EAN)	4050118630602
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2025-08-31T00:00:00+02:00

BVFL HYBRID CUSTOMER SAMPLE BOX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	154 g
------------	-------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Important note

Notes

Classifications

ETIM 8.0	EC002943	ETIM 9.0	EC002943
ETIM 10.0	EC002943	ECLASS 14.0	27-46-02-01
ECLASS 15.0	27-46-02-01		