



## LSF-SMT 3.81/04/90PN 3.5SN BK TU

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



### Your special benefits

- Cost-effective alternative to RJ45 and M12 connections
- Ethernet-compliant data transmission e.g. for PROFINET applications (Cat. 5, up to 100 Mbps)
- Proven PUSH IN wire connection
- Suitable for THT (LMF) and THR (LSF-SMT)soldering process
- Suitable for data transmission according to ISO / IEC 11801-1; DIN EN 50173-1 (VDE 0800-173-1) and ANSI/TIA-568-B.2-10
- Wide range of applications for all IIoT devices

### General ordering data

|              |   |
|--------------|---|
| Version      | Printed circuit board terminals, 3.81 mm, Number of poles: 4, 90°, Solder pin length (l): 3.5 mm, tinned, black, PUSH IN with push button, Clamping range, max. : 1.5 mm², Tube |
| Order No.    | <a href="#">2639530000</a>  |
| Type         | LSF-SMT 3.81/04/90PN 3.5SN BK TU  |
| GTIN (EAN)   | 4050118657296   |
| Qty.         | 35 items  |
| Product data | IEC: 320 V / 17.5 A / 0.2 - 1.5 mm²<br>UL: 300 V / 12 A / AWG 28 - AWG 14   |
| Packaging    | Tube  |

## LSF-SMT 3.81/04/90PN 3.5SN BK TU

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E60693

## Dimensions and weights

|                          |          |                 |             |
|--------------------------|----------|-----------------|-------------|
| Depth                    | 14.75 mm | Depth (inches)  | 0.5807 inch |
| Height                   | 12 mm    | Height (inches) | 0.4724 inch |
| Height of lowest version | 8.5 mm   | Net weight      | 2.87 g      |

## Temperatures

Continuous operating temp., max. 120 °C

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

## System specifications

|  |  |      |
|--|--|------|
| Number of poles                            | 4  |      |
| Solder pin length (l)                      | 3.5 mm   |      |
| Mounting onto the PCB                      | THT/THR solder connection                          |      |
| Pitch in inches (P)                        | 0.150 "  |      |
| Side termination, characteristic           | closed side  |      |
| Solder eyelet hole diameter tolerance (D)+ | 0,1 mm   |      |
| Transmission rate                          | 10 / 100 Mbps                                      |      |
| Number of solder pins per pole             | 2  |      |
| Solder eyelet hole diameter (D)            | 1.1 mm   |      |
| Category                                   | Cat. 5   |      |
| Product family                             | OMNIMATE Signal - series LSF                       |      |
| Pitch in mm (P)                            | 3.81 mm  |      |
| Protection degree                          | IP20   |      |
| Performance-Category                       | Cat. 5 10 / 100 Mbps                               |      |
| Soldering process                          | Reflow soldering, Manual soldering, Wave soldering |      |
| Solder pin dimensions                      | 0.35 x 0.8 mm                                      |      |
| Solder pin length tolerance                | Lower tolerance with prefix (reveals minimum)      | -0.3 |
|  | Upper tolerance with prefix (reveals maximum)      | 0    |
|  | Tolerance, unit                                    | mm   |
| Solder pin length tolerance                | 0 / -0.3 mm  |      |
| Solder pin dimensions = d tolerance        | Lower tolerance with prefix (reveals minimum)      | -0.1 |
|  | Upper tolerance with prefix (reveals maximum)      | 0    |
|  | Tolerance, unit                                    | mm   |

## Electrical properties

Volume resistance 1.60 mΩ

## LSF-SMT 3.81/04/90PN 3.5SN BK TU

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Material data

|                                       |          |                                       |                  |
|---------------------------------------|----------|---------------------------------------|------------------|
| Insulating material                   | LCP GF   | Colour                                | black            |
| Colour chart (similar)                | RAL 9011 | Insulating material group             | Illa             |
| Comparative Tracking Index (CTI)      | ≥ 175    | Moisture Level (MSL)                  | 1                |
| UL 94 flammability rating             | V-0      | Contact material                      | Copper alloy     |
| Contact surface                       | tinned   | Layer structure of solder connection  | 4...6 µm Sn matt |
| Storage temperature, min.             | -40 °C   | Storage temperature, max.             | 70 °C            |
| Operating temperature, min.           | -50 °C   | Operating temperature, max.           | 120 °C           |
| Temperature range, installation, min. | -30 °C   | Temperature range, installation, max. | 120 °C           |

### Conductors suitable for connection

|   |                      |
|---|----------------------|
| Clamping range, min.                            | 0.13 mm <sup>2</sup> |
| Clamping range, max.                            | 1.5 mm <sup>2</sup>  |
| Wire connection cross section AWG, min.         | AWG 28               |
| Wire connection cross section AWG, max.         | AWG 14               |
| Solid, min. H05(07) V-U                         | 0.2 mm <sup>2</sup>  |
| Solid, max. H05(07) V-U                         | 1.5 mm <sup>2</sup>  |
| Flexible, min. H05(07) V-K                      | 0.2 mm <sup>2</sup>  |
| Flexible, max. H05(07) V-K                      | 1.5 mm <sup>2</sup>  |
| w. plastic collar ferrule, DIN 46228 pt 4, min. | 0.25 mm <sup>2</sup> |
| w. plastic collar ferrule, DIN 46228 pt 4, max. | 0.75 mm <sup>2</sup> |
| w. wire end ferrule, DIN 46228 pt 1, min.       | 0.25 mm <sup>2</sup> |
| w. wire end ferrule, DIN 46228 pt 1, max.       | 1.5 mm <sup>2</sup>  |

| Clampable conductor                    | Cross-section for conductor connection | Type                         | fine-wired                    |
|--|--|------------------------------|-------------------------------|
|  |  | nominal                      | 0.25 mm <sup>2</sup>          |
| wire end ferrule                       |  | Stripping length             | nominal 10 mm                 |
|  |  | Recommended wire-end ferrule | <a href="#">H0,25/12 HBL</a>  |
|  |  |                              |                               |
| Cross-section for conductor connection |  | Type                         | fine-wired                    |
|  |  | nominal                      | 0.34 mm <sup>2</sup>          |
| wire end ferrule                       |  | Stripping length             | nominal 10 mm                 |
|  |  | Recommended wire-end ferrule | <a href="#">H0,34/12 TK</a>   |
|  |  |                              |                               |
| Cross-section for conductor connection |  | Type                         | fine-wired                    |
|  |  | nominal                      | 0.5 mm <sup>2</sup>           |
| wire end ferrule                       |  | Stripping length             | nominal 10 mm                 |
|  |  | Recommended wire-end ferrule | <a href="#">H0,5/14 OR</a>    |
|  |  |                              |                               |
| Cross-section for conductor connection |  | Type                         | fine-wired                    |
|  |  | nominal                      | 0.75 mm <sup>2</sup>          |
| wire end ferrule                       |  | Stripping length             | nominal 10 mm                 |
|  |  | Recommended wire-end ferrule | <a href="#">H0,75/14T HBL</a> |
|  |  |                              |                               |

Reference text Length of ferrules is to be chosen depending on the product and the rated voltage., The outside diameter of the plastic collar should not be larger than the pitch (P)

### Rated data acc. to IEC

|   |                        |   |        |
|---|------------------------|---|--------|
| tested acc. to standard                       | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C) | 17.5 A |
| Rated current, max. number of poles (Tu=20°C) | 16 A                   | Rated current, min. number of poles (Tu=40°C) | 17.5 A |

## LSF-SMT 3.81/04/90PN 3.5SN BK TU

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

### Technical data

|   |        |   |                  |
|---|--------|---|------------------|
| Rated current, max. number of poles (Tu=40°C)                             | 14 A   | Rated voltage for surge voltage class / pollution degree II/2         | 320 V            |
| Rated voltage for surge voltage class / pollution degree III/2            | 160 V  | Rated voltage for surge voltage class / pollution degree III/3        | 160 V            |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 2.5 kV | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 2.5 kV           |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 2.5 kV | Short-time withstand current resistance                               | 3 x 1s with 80 A |

#### Rated data acc. to CSA

|                                   |        |                                   |        |
|-----------------------------------|--------|-----------------------------------|--------|
| Rated voltage (Use group B / CSA) | 300 V  | Rated voltage (Use group D / CSA) | 300 V  |
| Rated current (Use group B / CSA) | 10 A   | Rated current (Use group D / CSA) | 10 A   |
| Wire cross-section, AWG, min.     | AWG 28 | Wire cross-section, AWG, max.     | AWG 14 |

#### Rated data acc. to UL 1059

|                                       |  |                                       |        |
|---------------------------------------|--|---------------------------------------|--------|
| Institute (cURus)                     | CURUS  | Certificate No. (cURus)               | E60693 |
| Rated voltage (Use group B / UL 1059) | 300 V  | Rated voltage (Use group D / UL 1059) | 300 V  |
| Rated current (Use group B / UL 1059) | 12 A   | Rated current (Use group D / UL 1059) | 10 A   |
| Wire cross-section, AWG, min.         | AWG 28   | Wire cross-section, AWG, max.         | AWG 14 |
| Reference to approval values          | Specifications are maximum values, details - see approval certificate. |                                       |        |

#### Packing

|           |          |            |           |
|-----------|----------|------------|-----------|
| Packaging | Tube     | VPE length | 557.00 mm |
| VPE width | 20.00 mm | VPE height | 15.00 mm  |

#### Type tests

|   |                |  |                               |  |
|---|----------------|--|-------------------------------|--|
| Test: Durability of markings                  | Standard       | DIN EN 60512-1-1 / 01.03   |                               |  |
|   | Test           | mark of origin, type identification, pitch, durability                             |                               |  |
|   | Evaluation     | available  |                               |  |
|   | Test           | approval marking UL  |                               |  |
| Test: Clampable cross section                 | Evaluation     | on packaging label   |                               |  |
|   | Standard       | DIN EN 60999-1 section 7 and 9.1 / 12.00, DIN EN 60947-1 section 8.2.4.5.1 / 12.02 |                               |  |
|   | Conductor type | Type of conductor and conductor cross-section                                      | solid 0.14 mm <sup>2</sup>    |  |
|   |                | Type of conductor and conductor cross-section                                      | stranded 0.14 mm <sup>2</sup> |  |
|   |                | Type of conductor and conductor cross-section                                      | solid 1.5 mm <sup>2</sup>     |  |
|   |                | Type of conductor and conductor cross-section                                      | stranded 1.5 mm <sup>2</sup>  |  |
|   |                | Type of conductor and conductor cross-section                                      | AWG 24/1                      |  |
|   |                | Type of conductor and conductor cross-section                                      | AWG 24/19                     |  |
| Type of conductor and conductor cross-section |                | AWG 16/1   |                               |  |

**LSF-SMT 3.81/04/90PN 3.5SN BK TU**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

|   |   |   |                               |  |
|---|---|---|-------------------------------|--|
|   |   | Type of conductor and conductor cross-section | AWG 16/19                     |  |
| Test for damage to and accidental loosening of conductors | Evaluation                                    | passed  |                               |  |
|   | Standard                                      | DIN EN 60999-1 section 9.4 / 12.00            |                               |  |
|   | Requirement                                   | 0.2 kg  |                               |  |
|   | Conductor type                                | Type of conductor and conductor cross-section | AWG 24/1                      |  |
|   |   | Type of conductor and conductor cross-section | AWG 24/19                     |  |
|   | Evaluation                                    | passed  |                               |  |
|   | Requirement                                   | 0.3 kg  |                               |  |
|   | Conductor type                                | Type of conductor and conductor cross-section | stranded 0.25 mm <sup>2</sup> |  |
|   |   | Type of conductor and conductor cross-section | solid 0.5 mm <sup>2</sup>     |  |
|   | Evaluation                                    | passed  |                               |  |
| Requirement   | 0.4 kg  |   |                               |  |
| Conductor type  | Type of conductor and conductor cross-section | solid 1.5 mm <sup>2</sup>                     |                               |  |
|   | Type of conductor and conductor cross-section | stranded 1.5 mm <sup>2</sup>                  |                               |  |
|   | Type of conductor and conductor cross-section | AWG 16/1                                      |                               |  |
|   | Type of conductor and conductor cross-section | AWG 16/19                                     |                               |  |
| Evaluation  | passed  |   |                               |  |
| Pull-out test   | Standard                                      | DIN EN 60999-1 section 9.5 / 12.00            |                               |  |
|   | Requirement                                   | ≥10 N   |                               |  |
|   | Conductor type                                | Type of conductor and conductor cross-section | AWG 24/1                      |  |
|   |   | Type of conductor and conductor cross-section | AWG 24/19                     |  |
|   | Evaluation                                    | passed  |                               |  |
|   | Requirement                                   | ≥20 N   |                               |  |
|   | Conductor type                                | Type of conductor and conductor cross-section | stranded 0.25 mm <sup>2</sup> |  |
|   |   | Type of conductor and conductor cross-section | H05V-U0.5                     |  |
|   | Evaluation                                    | passed  |                               |  |
|   | Requirement                                   | ≥40 N   |                               |  |
| Conductor type  | Type of conductor and conductor cross-section | H07V-U1.5                                     |                               |  |
|   | Type of conductor and conductor cross-section | H07V-K1.5                                     |                               |  |
|   | Type of conductor and conductor cross-section | AWG 16/1                                      |                               |  |

**LSF-SMT 3.81/04/90PN 3.5SN BK TU**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

|            |   |           |
|------------|---|-----------|
|            | Type of conductor and conductor cross-section | AWG 16/19 |
| Evaluation | passed  |           |

**Important note**

**IPC conformity** Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

- Notes**
- Additional push button colours on request
  - Operating force of slider max. 40 N
  - Rated current related to rated cross-section & min. No. of poles.
  - Wire end ferrule with plastic collar to DIN 46228/4
  - Wire end ferrule without plastic collar to DIN 46228/1
  - P on drawing = pitch
  - Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
  - Crimping shape "A" for wire end ferrules with PZ 6/5 crimping tool recommended.
  - Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002643    | ETIM 9.0    | EC002643    |
| ETIM 10.0   | EC002643    | ECLASS 14.0 | 27-46-01-01 |
| ECLASS 15.0 | 27-46-01-01 |             |             |


LSF-SMT 3.81/04/90PN 3.5SN BK TU

Weidmüller Interface GmbH & Co. KG  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

Drawings

Product image



Dimensioned drawing

