


FBCON PA CG 4WAY LIMITER
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com


For standard industrial applications (non-hazardous areas), PROFIBUS PA junction boxes and limiters are available as 1-way, 2-way, 4-way, and 8-way distributors. FBCon limiters are designed to protect connected field devices from over voltages and short circuits. As voltage-limiting protective elements, suppressor diodes are used. Due to the integrated current limitation, the segment is also protected against short circuit on a spur line. EMC cable glands, protection class IP66 and a wide operating temperature range safely protect your connections in harsh environments.

Functionality

- EMC cable glands for trunk and spurs
- M12 connector for spurs
- External earthing stud
- Pressure equalizing element
- Protection class IP66
- Aluminium and stainless-steel versions
- Profibus PA / Foundation Fieldbus compatible

Note: The use of FBCon products with aluminum enclosures and / or M12 connectors is not recommended in strongly saline environments.

General ordering data

| | |
|------------|--|
| Version | Standard distributor with current limiting, 4-channel distributor LIMITER, IP66, IP67, Round |
| Order No. | 2624380000 |
| Type | FBCON PA CG 4WAY LIMITER |
| GTIN (EAN) | 4050118627909 |
| Qty. | 1 items |

FBCON PA CG 4WAY LIMITER

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E141197

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 34 mm | Depth (inches) | 1.3386 inch |
| Height | 34 mm | Height (inches) | 1.3386 inch |
| Width | 125 mm | Width (inches) | 4.9212 inch |
| Net weight | 688 g | | |

Temperatures

| | | | |
|---------------------|---------------------------|-----------------------|----------------|
| Storage temperature | -40 °C...80 °C | Operating temperature | -40 °C...75 °C |
| Humidity | 5...95 %, no condensation | | |

Probability of failure

SIL in compliance with IEC 61508 None

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6bl, 6c, 7a, 7cl |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 3a5f5913-76fc-4ff5-8563-4463f80bbe02 |

Connection data

| | | | |
|----------------------|-------------------|----------------------|-------------------|
| Clamping range, min. | 4 mm ² | Clamping range, max. | 6 mm ² |
|----------------------|-------------------|----------------------|-------------------|

Technical data

| | | | |
|-----------------------------------|------------------------------------|----------------------|---------------------------------------|
| Number of poles | 3 | Cable glands | Brass cable gland |
| Type of distribution | 4-channel distributor LIMITER | Design of housing | With pressure compensation element |
| Housing main material | Aluminium | Cable entry | Round |
| Conductor O.D., max. | 9.5 mm | Conductor O.D., min. | 6.5 mm |
| Type of mounting | surface-mounted | Protection degree | IP66, IP67 |
| Pollution severity | 3 | Bus system | Profibus-PA, Foundation Fieldbus |
| Current limiting | adjustable, 20 mA, 40 mA, 60 mA | Operating voltage | 30 V |
| Power consumption in standby mode | 7 mA | Housing surface | powder coating |

Part description

| | |
|---------------------|--|
| Product description | The device is an active field distributor for the fieldbus systems Profibus PA and Foundation Fieldbus H1. The device complies with protection class IP66/IP67. Functional description The device connects up to eight field devices with one fieldbus segment. An adjustable current monitoring per spur line protects the trunk line from short circuits or overload (see figure B1). Suppressor diodes protect the connected field devices from surge voltages. A red LED indicates |
|---------------------|--|

FBCON PA CG 4WAY LIMITER**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data**

a short circuit or overload on the spur line. A green LED indicates sufficient voltage supply on the trunk line. The device supports earthing concepts with multi-point screen earthing or single-point screen earthing. The earthing concepts are explained in the Profibus PA and Foundation Fieldbus guidelines.

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001604 | ETIM 7.0 | EC001604 |
| ETIM 8.0 | EC001604 | ETIM 9.0 | EC001604 |
| ETIM 10.0 | EC001604 | ECLASS 9.0 | 27-24-26-08 |
| ECLASS 9.1 | 27-24-26-08 | ECLASS 10.0 | 27-24-26-08 |
| ECLASS 11.0 | 27-24-26-08 | ECLASS 12.0 | 27-44-01-11 |
| ECLASS 13.0 | 27-44-01-11 | ECLASS 14.0 | 27-44-01-11 |
| ECLASS 15.0 | 27-44-01-11 | | |

FBCON PA CG 4WAY LIMITER

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

