

## FBCON PA CG 4WAY LIMITER

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



For standard industrial applications (non-hazardous areas), PROFIBUS PA junction boxes and limiters are available as 1-way, 2-way, 4-way, and 8-way distributors. FBCon limiters are designed to protect connected field devices from over voltages and short circuits. As voltage-limiting protective elements, suppressor diodes are used. Due to the integrated current limitation, the segment is also protected against short circuit on a spur line. EMC cable glands, protection class IP66 and a wide operating temperature range safely protect your connections in harsh environments.

### Functionality

- EMC cable glands for trunk and spurs
- M12 connector for spurs
- External earthing stud
- Pressure equalizing element
- Protection class IP66
- Aluminium and stainless-steel versions
- Profibus PA / Foundation Fieldbus compatible

Note: The use of FBCon products with aluminum enclosures and / or M12 connectors is not recommended in strongly saline environments.

### General ordering data

Version	Standard distributor with current limiting, 4-channel distributor LIMITER, IP66, IP67, Round
Order No.	<a href="#">2624380000</a>
Type	FBCON PA CG 4WAY LIMITER
GTIN (EAN)	4050118627909
Qty.	1 items

## FBCON PA CG 4WAY LIMITER

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E141197

## Dimensions and weights

Depth	34 mm	Depth (inches)	1.3386 inch
Height	34 mm	Height (inches)	1.3386 inch
Width	125 mm	Width (inches)	4.9212 inch
Net weight	688 g		

## Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...75 °C
Humidity	5...95 %, no condensation		

## Probability of failure

SIL in compliance with IEC 61508 None

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6bl, 6c, 7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	3a5f5913-76fc-4ff5-8563-4463f80bbe02

## Connection data

Clamping range, min.	4 mm <sup>2</sup>	Clamping range, max.	6 mm <sup>2</sup>
----------------------	-------------------	----------------------	-------------------

## Technical data

Number of poles	3	Cable glands	Brass cable gland
Type of distribution	4-channel distributor LIMITER	Design of housing	With pressure compensation element
Housing main material	Aluminium	Cable entry	Round
Conductor O.D., max.	9.5 mm	Conductor O.D., min.	6.5 mm
Type of mounting	surface-mounted	Protection degree	IP66, IP67
Pollution severity	3	Bus system	Profibus-PA, Foundation Fieldbus
Current limiting	adjustable, 20 mA, 40 mA, 60 mA	Operating voltage	30 V
Power consumption in standby mode	7 mA	Housing surface	powder coating

## Part description

Product description The device is an active field distributor for the fieldbus systems Profibus PA and Foundation Fieldbus H1. The device complies with protection class IP66/IP67. Functional description The device connects up to eight field devices with one fieldbus segment. An adjustable current monitoring per spur line protects the trunk line from short circuits or overload (see figure B 1). Suppressor diodes protect the connected field devices from surge voltages. A red LED indicates

**FBCON PA CG 4WAY LIMITER**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

a short circuit or overload on the spur line. A green LED indicates sufficient voltage supply on the trunk line. The device supports earthing concepts with multi-point screen earthing or single-point screen earthing. The earthing concepts are explained in the Profibus PA and Foundation Fieldbus guidelines.

**Classifications**

ETIM 8.0	EC001604	ETIM 9.0	EC001604
ETIM 10.0	EC001604	ECLASS 14.0	27-44-01-11
ECLASS 15.0	27-44-01-11		

FBCON PA CG 4WAY LIMITER

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

Drawings

