

## AMR 2.5/50

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



AMR marking rails are made for the Klippon Connect terminals, type A-series.

There are 5 sizes available for terminals from 1.5 mm<sup>2</sup> up to 10 mm<sup>2</sup>.

Each rail has a specific feet construction that fits perfectly into the marking channel of the suitable terminal.

The length is designed to be used for 50 terminals. The marking rail can be cut for smaller rails.

Marking strips with a width of 9.5 mm can be inserted into the rail for a flexible identification of each terminal.

### General ordering data

Version	Accessories, Terminal marker, 10.5 x 255 mm, Pitch in mm (P): 5.10 Weidmueller Klippon Connect, white
Order No.	<a href="#">2655010000</a>
Type	AMR 2.5/50
GTIN (EAN)	4050118692709
Qty.	10 items

## AMR 2.5/50

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Height	10.5 mm	Height (inches)	0.4134 inch
Width	255 mm	Width (inches)	10.0394 inch
Net weight	4 g		

### Temperatures

Operating temperature range	-40...82 °C
-----------------------------	-------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General data

Orientation of print	horizontal and vertical	
Version	Weidmueller Klippon Connect terminals, type A-series	
Width	255 mm	
UL 94 flammability rating	V-0	
Operating temperature range, max.	82 °C	
Operating temperature range, min.	-40 °C	
Colour	white	
Halogen	No	
Basic material	PVC	
Printed characters	without	
Number of markers per packaging unit	Form of supply	Component part
Number of markers per combination	1 Component part = Terminal marker	
Operating temperature range	-40...82 °C	
Application/manufacturer	Weidmueller Klippon Connect	

### Connector markers

Pitch in mm (P)	5.10 mm
-----------------	---------

### Classifications

ETIM 8.0	EC000761	ETIM 9.0	EC000761
ETIM 10.0	EC000761	ECLASS 14.0	27-28-11-01
ECLASS 15.0	27-28-11-01		

Example of use

