

CB-UVR 365/7,5 BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



UV-resistant polyamide 6.6 ensures long durability of our special cable ties even with strong UV radiation. Ideal for continuous outdoor use.

General ordering data

| | |
|------------|---|
| Version | Cable ties, 7.5 x 365 mm, Polyamide 66, 540 N |
| Order No. | 2659360000 |
| Type | CB-UVR 365/7,5 BK |
| GTIN (EAN) | 4050118682823 |
| Qty. | 100 items |

CB-UVR 365/7,5 BK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data
Approvals

Approvals



| | |
|-----------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E317499 |

Dimensions and weights

| | | | |
|------------|--------|-----------------|--------------|
| Depth | 1 mm | Depth (inches) | 0.0394 inch |
| Height | 365 mm | Height (inches) | 14.3701 inch |
| Width | 7.5 mm | Width (inches) | 0.2953 inch |
| Net weight | 4.21 g | | |

Temperatures

| | | | |
|----------------------------------|-------------|----------------------------------|--------|
| Operating temperature range | -40...85 °C | Continuous operating temp., min. | -40 °C |
| Continuous operating temp., max. | 105 °C | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Installation materials

| | | | |
|-----------------------------------|---------|-----------------------------------|--------------|
| UV-resistant | Yes | For re-opening | No |
| UL 94 flammability rating | V-2 | Operating temperature range, max. | 85 °C |
| Operating temperature range, min. | -40 °C | Halogen | No |
| Cable diameter, max. | 100 mm | Basic material | Polyamide 66 |
| Tensile strength | 540 N | Bundle diameter, max. | 100 mm |
| Tensile strength (Pound-force) | 121 lbf | Bundle diameter, min. | 8 mm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000046 | ETIM 9.0 | EC000046 |
| ETIM 10.0 | EC000046 | ECLASS 14.0 | 27-14-07-02 |
| ECLASS 15.0 | 27-14-07-02 | | |

Drawings

