

**CB-VT 98/2,5 WT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

Our self-extinguishing cable ties are suitable for environments with increased fire protection requirements. They comply with EN45545 and are suitable for use in rail vehicles.

**General ordering data**

Version	Cable ties, 2.5 x 98 mm, Polyamide 66, 80 N
Order No.	<a href="#">2659490000</a>
Type	CB-VT 98/2,5 WT
GTIN (EAN)	4050118682953
Qty.	100 items

## CB-VT 98/2,5 WT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	1 mm	Depth (inches)	0.0394 inch
Height	98 mm	Height (inches)	3.8583 inch
Width	2.5 mm	Width (inches)	0.0984 inch
Net weight	0.24 g		

### Temperatures

Operating temperature range	-40...85 °C	Continuous operating temp., min.	-40 °C
Continuous operating temp., max.	85 °C		

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Installation materials

UV-resistant	No	For re-opening	No
UL 94 flammability rating	V-0	Operating temperature range, max.	85 °C
Operating temperature range, min.	-40 °C	Halogen	No
Cable diameter, max.	21 mm	Basic material	Polyamide 66
Tensile strength	80 N	Bundle diameter, max.	21 mm
Tensile strength (Pound-force)	18 lbf	Bundle diameter, min.	1 mm

### Classifications

ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		

**Drawings**

