

IE-PS-M12X-180-P-TH-CG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The 8pole M12 Mini crimp cable connector with X-coding and 90° cable exit is with compact dimensions and 8 cable exit positions predestined for difficult installation conditions. The cable clamp version with the wide cable clamp ranges from 4 up to 9 mm plus the fully shielded housing together with the shielded strain relief is the universal fail-safe solution for all common cables on the market.

General ordering data

Order No.	2664820000
Type	IE-PS-M12X-180-P-TH-CG
GTIN (EAN)	4050118765229
Qty.	1 items

IE-PS-M12X-180-P-TH-CG

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Diameter	15 mm	Net weight	15 g
----------	-------	------------	------

Temperatures

Storage temperature	Operating temperature	-40 °C...85 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

Technical data customisable plug-in connectors

Number of poles	8	Coding	X-coded
Contact surface	Ni/Au	LED	No
Type of connection	Crimp connection	Housing main material	Cu alloy Ni plated
Insulation resistance	≥ 100 MΩ	Cable diameter, max.	9 mm
Cable diameter, min.	4 mm	Category	Cat. 6A
Conductor cross-section, max.	0.34 mm ²	Conductor cross-section, min.	0.14 mm ²
Nominal voltage	48 V	Nominal current	0.5 A
Protection degree	IP67	Plugging cycles	≥ 250
Pollution severity	3	Rated current	0.5 A
Gender of contact	Male	Shield connection	Yes
Threaded ring material	Nickel-plated CuZn		

General Info

Number of poles	8	Connection 1	M12
Connection 2	Crimp	UL 94 flammability rating	V-0
Housing main material	Cu alloy Ni plated	Category	Cat. 6A
Connection thread	M12	Contact surface	Ni/Au
Wire connection cross section, finely stranded, min.	0.14 mm ²	Wire connection cross section, finely stranded, max.	0.34 mm ²
Wire cross-section, solid, min.	0.34 mm ²	Wire cross-section, solid, max.	0.32 mm ²
Conductor connection cross-section, flexible	0.14...0.34 mm ²	Protection degree	IP67
Plugging cycles	≥ 250		

Electrical properties

Insulation resistance	≥ 100 MΩ	Nominal voltage	48 V
Rated current	0.5 A		

General standards

Connector standard	IEC 61076-2-109
--------------------	-----------------

IE-PS-M12X-180-P-TH-CG

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Standards**

Connector standard	IEC 61076-2-109	Fire safety for railway vehicles	EN 45545 HL3
Shock and vibration proof according to	EN 50155:2001, DIN EN 61373		

Classifications

ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		


IE-PS-M12X-180-P-TH-CG

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing



Pole scheme

