


**THM WO VIN 12.7/19 WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

**General ordering data**

Version	THM, Conductor and cable markers, 2 - 4 mm, 12.7 x 19.1 mm, white
Order No.	<a href="#">2657 100000</a>
Type	THM WO VIN 12.7/19 WS
GTIN (EAN)	4050118675238
Qty.	10000 items

## THM WO VIN 12.7/19 WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	0.07 mm	Depth (inches)	0.0028 inch
Height	12.7 mm	Height (inches)	0.5 inch
Width	19.1 mm	Width (inches)	0.752 inch
Net weight	0.05 g		

### Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General data

Adhesive	Polyacrylate adhesive	
Type of printing	neutral	
Printing method	Thermal transfer	
Version	Self-adhesive	
Width	19.1 mm	
UL 94 flammability rating	V-0	
Operating temperature range, max.	80 °C	
Operating temperature range, min.	-40 °C	
Colour	white	
Halogen	Yes	
Basic material	Vinyl film	
Printed characters	without	
Number of markers per packaging unit	Form of supply	Label reel
Approval acc. to UL 969	No	
compatible printer	<a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a>	
Number of markers per combination	1 Label reel = Conductor and cable markers	
Operating temperature range	-40...80 °C	
Number per roll	100000	

### Conductor and cable markers

Wire connection cross section AWG, max.	AWG 14	Halogen	Yes
Wire connection cross section AWG, min.	AWG 18	Conductor cross-section, max.	12 mm <sup>2</sup>
Conductor O.D., max.	4 mm	Conductor O.D., min.	2 mm
Conductor O.D.	2 - 4 mm	Cross-section for connected wire	12 mm <sup>2</sup>

### Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

**Drawings**

