


**THM WO VIN 12.7/38.1 WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

**General ordering data**

Version	THM, Conductor and cable markers, 4 - 8 mm, 12.7 x 38.1 mm, white
Order No.	<a href="#">2657110000</a>
Type	THM WO VIN 12.7/38.1 WS
GTIN (EAN)	4050118675245
Qty.	10000 items

**THM WO VIN 12.7/38.1 WS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	0.07 mm	Depth (inches)	0.0028 inch
Height	12.7 mm	Height (inches)	0.5 inch
Width	38.1 mm	Width (inches)	1.5 inch
Net weight	0.11 g		

**Temperatures**

Operating temperature range -40...80 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

Adhesive	Polyacrylate adhesive		
Type of printing	neutral		
Printing method	Thermal transfer		
Version	Self-adhesive		
Width	38.1 mm		
UL 94 flammability rating	V-0		
Operating temperature range, max.	80 °C		
Operating temperature range, min.	-40 °C		
Colour	white		
Halogen	Yes		
Basic material	Vinyl film		
Printed characters	without		
Number of markers per packaging unit	Form of supply	Label reel	
Approval acc. to UL 969	No		
compatible printer	<a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a>		
Number of markers per combination	1 Label reel = Conductor and cable markers		
Operating temperature range	-40...80 °C		
Number per roll	10000		

**Conductor and cable markers**

Wire connection cross section AWG, max.	AWG 6	Halogen	Yes
Wire connection cross section AWG, min.	AWG 10	Conductor cross-section, max.	50 mm <sup>2</sup>
Conductor O.D., max.	8 mm	Conductor O.D., min.	4 mm
Conductor O.D.	4 - 8 mm	Cross-section for connected wire	50 mm <sup>2</sup>

**Classifications**

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

**Drawings**

