

THM WO VIN 25.4/57.2 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 6 - 12 mm, 25.4 x 57.2 mm, white
Order No.	2657180000
Type	THM WO VIN 25.4/57.2 WS
GTIN (EAN)	4050118675917
Qty.	2000 items

THM WO VIN 25.4/57.2 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	0.07 mm	Depth (inches)	0.0028 inch
Height	25.4 mm	Height (inches)	1 inch
Width	57.2 mm	Width (inches)	2.252 inch
Net weight	0.19 g		

Temperatures

Operating temperature range -40...80 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Adhesive	Polyacrylate adhesive		
Type of printing	neutral		
Printing method	Thermal transfer		
Version	Self-adhesive		
Width	57.2 mm		
UL 94 flammability rating	V-0		
Operating temperature range, max.	80 °C		
Operating temperature range, min.	-40 °C		
Colour	white		
Halogen	Yes		
Basic material	Vinyl film		
Printed characters	without		
Number of markers per packaging unit	Form of supply	Label reel	
Approval acc. to UL 969	No		
compatible printer	THM MULTIMARK , THM MULTIMARK PLUS		
Number of markers per combination	1 Label reel = Conductor and cable markers		
Operating temperature range	-40...80 °C		
Number per roll	2000		

Conductor and cable markers

Wire connection cross section AWG, max.	AWG 4	Halogen	Yes
Wire connection cross section AWG, min.	AWG 8	Conductor cross-section, max.	113 mm ²
Conductor O.D., max.	12 mm	Conductor O.D., min.	6 mm
Conductor O.D.	6 - 12 mm	Cross-section for connected wire	113 mm ²

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

