

## CB-HTR 200/3,6 BK

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Our heat-stabilised cable ties made of polyamide 6.6 are suitable for continuous use at temperatures up to +125°C.

### General ordering data

Version	Cable ties, 3.5 x 200 mm, Polyamide 66, 180 N
Order No.	<a href="#">2659390000</a>
Type	CB-HTR 200/3,6 BK
GTIN (EAN)	4050118682854
Qty.	100 items

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Depth	1 mm	Depth (inches)	0.0394 inch
Height	200 mm	Height (inches)	7.874 inch
Width	3.5 mm	Width (inches)	0.1378 inch
Net weight	0.9 g		

**Temperatures**

Operating temperature range	-40...125 °C	Continuous operating temp., min.	-40 °C
Continuous operating temp., max.	125 °C		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Installation materials**

UV-resistant	No	For re-opening	No
UL 94 flammability rating	V-2	Operating temperature range, max.	125 °C
Operating temperature range, min.	-40 °C	Halogen	No
Cable diameter, max.	50 mm	Basic material	Polyamide 66
Tensile strength	180 N	Bundle diameter, max.	50 mm
Tensile strength (Pound-force)	40 lbf	Bundle diameter, min.	3 mm

**Classifications**

ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		

**Drawings**

