

## V-TEST II ADP

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



### V-TEST II

- Testing device for pluggable overvoltage protection VPU AC and VPU PV series
- Device for implementing the IEC 62305-3 standard (Periodic test)
- Handy device with integrated rechargeable battery set for on-site use measurements
- QR code leads to check value table
- Intuitive user guidance (English)

The V-TEST II is a compact, portable test unit for pluggable overvoltage protection of VPU AC and VPU PV series. The test device can be used to test surge protection in accordance with the test periods required by IEC62305-3. The measuring result of the protective element is shown in a backlit display. To determine the status of the protective element, the measurement result must be verified with the aid of the test table.

### General ordering data

Version	Lightning and surge protection, Adapter
Order No.	<a href="#">2661050000</a>
Type	V-TEST II ADP
GTIN (EAN)	4050118704150
Qty.	1 items

**V-TEST II ADP**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	60 mm	Depth (inches)	2.3622 inch
Height	52 mm	Height (inches)	2.0472 inch
Width	109 mm	Width (inches)	4.2913 inch
Net weight	500 g		

**Temperatures**

Storage temperature	-10 °C...60 °C	Operating temperature	0 °C...40 °C
Humidity	25 - 75%, no condensation		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

**General data**

UL 94 flammability rating	V-0	Colour	black
Protection degree	IP20		

**Rated data IEC / EN**

Standards	EN 61010-1, EN 61326-1
-----------	------------------------

**Technical specifications for tester**

UL 94 flammability rating	V-0
---------------------------	-----

**General data**

Protection degree	IP20	Colour	black
-------------------	------	--------	-------

**Classifications**

ETIM 8.0	EC002495	ETIM 9.0	EC002495
ETIM 10.0	EC002495	ECLASS 14.0	27-20-11-14
ECLASS 15.0	27-20-11-14		