


**IE-FCI-PWB-DK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

**General ordering data**

Version	FrontCom, Insert Power large, Type K, Socket connector, DK
Order No.	<a href="#">2661340000</a>
Type	IE-FCI-PWB-DK
GTIN (EAN)	4050118675429
Qty.	1 items

## IE-FCI-PWB-DK

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

Net weight 28.09 g

## Temperatures

Storage temperature Operating temperature -5 °C...40 °C

Installation temperature

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

## General data

Protection degree IP20 Insert type Insert Power large

Connector face Type K

## Clampable conductors

Stripping length 13 mm

Type of connection PUSH IN

Conductor connection cross-section, extremely flexible with wire end ferrule min. 1.5 mm<sup>2</sup>  
max. 1.5 mm<sup>2</sup>Conductor connection cross-section, extremely flexible without wire end ferrule min. 1.5 mm<sup>2</sup>  
max. 2.5 mm<sup>2</sup>Conductor connection cross-section, rigid min. 1.5 mm<sup>2</sup>  
max. 2.5 mm<sup>2</sup>Conductor connection cross-section, flexible with wire end ferrule min. 1.5 mm<sup>2</sup>  
max. 1.5 mm<sup>2</sup>Conductor connection cross-section, flexible without wire end ferrule 1.5 ... 2.5 mm<sup>2</sup>Conductor connection cross-section, extremely flexible without wire end ferrule 1.5 ... 2.5 mm<sup>2</sup>Conductor connection cross-section, rigid 1.5 ... 2.5 mm<sup>2</sup>Conductor connection cross-section, flexible with wire end ferrule 1.5 ... 1.5 mm<sup>2</sup>Conductor connection cross-section, flexible without wire end ferrule min. 1.5 mm<sup>2</sup>  
max. 2.5 mm<sup>2</sup>Conductor connection cross-section, extremely flexible with wire end ferrule 1.5 ... 1.5 mm<sup>2</sup>

## Technical data

Rated voltage (AC) 250 V Housing main material Polycarbonate PC

Nominal current 13 A


**Technical data**

**Classifications**

ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 14.0	27-18-28-92
ECLASS 15.0	27-18-28-92		

**Drawings**

**Dimensioned drawing**



**Dimensioned drawing**

