

**SAIBGC-M-4D-4/9-M12-WDF-CG****Weidmüller Interface GmbH & Co. KG**

Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

The crimp connection is characterised by high functional reliability. With this connection technology, the conductor is crimped to the contact and then engaged in the contact carrier. The connection between the conductor and crimp is vibration-resistant and boasts long-term stability.

Crimp contacts are to be ordered separately.

**General ordering data**

Version	Field attachable connector, M12
Order No.	<a href="#">2664780000</a>
Type	SAIBGC-M-4D-4/9-M12-WDF-CG
GTIN (EAN)	4050118765236
Qty.	1 items

**SAIBGC-M-4D-4/9-M12-WDF-CG**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergsstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Approvals**

RoHS	Conform
------	---------

**Dimensions and weights**

Diameter	21 mm	Net weight	20.5 g
----------	-------	------------	--------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	Oea6d931-f9e9-40a6-89d9-8d67103189d3

**Technical data customisable plug-in connectors**

Number of poles	4	Coding	D-coded
Contact surface	Ni/Au	LED	No
Type of connection	Crimp connection	Housing main material	Cu alloy Ni plated
Cable diameter, max.	9 mm	Cable diameter, min.	4 mm
Conductor cross-section, max.	0.82 mm <sup>2</sup>	Conductor cross-section, min.	0.08 mm <sup>2</sup>
Nominal voltage	50 V	Nominal current	4 A
Protection degree	IP67	Plugging cycles	≥ 250
Gender of contact	Female	Shield connection	Yes
Threaded ring material	Nickel-plated CuZn	Temperature range of housing	-40 ... +85 °C

**General Info**

Number of poles	4	Connection 1	M12
Connection 2	Crimp	UL 94 flammability rating	V-0
Housing main material	Cu alloy Ni plated	Connection thread	M12
Contact surface	Ni/Au	Wire connection cross section, finely stranded, min.	0.08 mm <sup>2</sup>
Wire connection cross section, finely stranded, max.	0.82 mm <sup>2</sup>	Protection degree	IP67
Plugging cycles	≥ 250		

**Electrical properties**

Nominal voltage	50 V
-----------------	------

**General standards**

Connector standard	IEC 61076-2-101
--------------------	-----------------

**Standards**

Connector standard	IEC 61076-2-101	Fire safety for railway vehicles	EN 45545 HL3
Shock and vibration proof according to	EN 50155:2001, DIN EN 61373		




**Classifications**

ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		

**SAIBGC-M-4D-4/9-M12-WDF-CG**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings****Dimensioned drawing****Pole scheme****Pole scheme**

## SAIBGC-M-4D-4/9-M12-WDF-CG

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Shield cable gland



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

The crimp connection is characterised by high functional reliability. With this connection technology, the conductor is crimped to the contact and then engaged in the contact carrier. The connection between the conductor and crimp is vibration-resistant and boasts long-term stability.

Crimp contacts are to be ordered separately.

## General ordering data

Type	SAI-M12-KBC-18/20	Version
Order No.	<a href="#">2664860000</a>	Contact
GTIN (EAN)	4050118755206	
Qty.	100 ST	
Type	SAI-M12-KBC-20/22	Version
Order No.	<a href="#">2664870000</a>	Contact
GTIN (EAN)	4050118755213	
Qty.	100 ST	
Type	SAI-M12-KBC-22/24	Version
Order No.	<a href="#">2673730000</a>	Contact
GTIN (EAN)	4050118754599	
Qty.	100 ST	
Type	SAI-M12-KBC-26/28	Version
Order No.	<a href="#">2673740000</a>	Contact
GTIN (EAN)	4050118755084	
Qty.	100 ST	

## ...for M12



Weidmüller offers a wide range of tools and accessories for sensor-actuator cabling.

## General ordering data

Type	SAI-TMCSK	Version
Order No.	<a href="#">1381690000</a>	Pressing tool, 4-indent crimp
GTIN (EAN)	4050118183870	
Qty.	1 ST	