

**SAIBGP-P-5A-3/8-M12**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

**General ordering data**

Version	Field attachable connector, M12
Order No.	<a href="#">2681580000</a>
Type	SAIBGP-P-5A-3/8-M12
GTIN (EAN)	4050118759754
Qty.	1 items

**SAIBGP-P-5A-3/8-M12**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate no. (cULus)	E307231

**Dimensions and weights**

Diameter	19 mm	Net weight	19 g
----------	-------	------------	------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Technical data customisable plug-in connectors**

Number of poles	5	
Coding	A	
Contact surface	Ni/Au	
LED	No	
Type of connection	PUSH IN	
Housing main material	PA 66	
Insulation resistance	≥ 100 MΩ	
Cable diameter, max.	8 mm	
Cable diameter, min.	3 mm	
Conductor cross-section, max.	0.75 mm <sup>2</sup>	
Conductor cross-section, min.	0.14 mm <sup>2</sup>	
Nominal voltage	48 V	
Nominal current	4 A	
Protection degree	IP67	
Plugging cycles	≥ 100	
Pollution severity	3	
Gender of contact	Female	
Rated voltage	Rated voltage	48 V
	Voltage type	AC
	Rated voltage	60 V
	Voltage type	DC
Shield connection	No	
Threaded ring material	Diecast zinc	
Temperature range of housing	-40 ... +85 ° C	
Mounting position, installation notice	The connector pin assignment can be rotated 45° to the cable outlet	

**General Info**

Number of poles	5	Connection 1	M12
Connection 2	PUSH IN	UL 94 flammability rating	V-0
Housing main material	PA 66	Connection thread	M12
Contact surface	Ni/Au	Wire connection cross section, finely stranded, min.	0.14 mm <sup>2</sup>

## SAIBGP-P-5A-3/8-M12

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

Wire connection cross section, finely stranded, max.	0.75 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.08 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	0.5 mm <sup>2</sup>	Wire cross-section, solid, min.	0.14 mm <sup>2</sup>
Wire cross-section, solid, max.	0.75 mm <sup>2</sup>	Protection degree	IP67
Plugging cycles	≥ 100		

### Standards

Connector standard	IEC 61076-2-101	Fire safety for railway vehicles	DIN EN 45545-2
Shock and vibration proof according to	EN 50155:2001		

### Classifications

ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		


**SAIBGP-P-5A-3/8-M12**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Drawing**



**Pole scheme**

