

IE-SFP-1FE-SM-30

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Features of SFP-Transceiver series

- Huge variety of transceiver types for several transmission speeds (up to 10 Gigabit Ethernet) and distances (up to 60 km)
- BiDi SFP models for communication via single fiber
- Easy control of transceiver status due to support of Digital Diagnostic Monitoring (DDM)
- Hot pluggable (during operation)
- Class 1 laser product, EN60825-1 compliant
- Applicable for switches of the Eco-, Advanced- and SubstationLine

General ordering data

Version	SFP Transceiver, 100 Mbps, Singlemode, LC-Duplex, 30 km, -40 °C...85 °C
Order No.	2682460000
Type	IE-SFP-1FE-SM-30
GTIN (EAN)	4050118692259
Qty.	1 items

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E230683

Dimensions and weights

Net weight	17.5 g
------------	--------

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity	5 to 95 % (non-condensing)		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

EMC conformity and approvals

EMC standards	EN 55032, EN 55035	Safety standard	UL 62368-1
---------------	--------------------	-----------------	------------

Environmental conditions

Operating temperature, max.	85 °C	Operating temperature, min.	-40 °C
Humidity	5 to 95 % (non-condensing)	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

Fibre optic transceiver characteristics

Transmission rate	100 Mbps	
Digital diagnostic monitor function (DDM)	Supported	
Transceiver type	Singlemode	
Connector type	LC-Duplex	
Transmission distance, typ.	30 km	
Wavelength	typ.	1310 nm
	Wavelength	TX
	min.	1280 nm
	max.	1340 nm
	Wavelength	RX
	min.	1260 nm
Receive power	min.	-34 dBm
	max.	-3 dBm
Transmission power	min.	-15 dBm
	max.	-8 dBm
Link-budget	19 dB	

IE-SFP-1FE-SM-30

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Guarantee

Time interval 3 years

Power supply

Supply voltage 3.3 V (via Ethernet switch)

Technical data

Type of mounting Insert in SFP slot

Classifications

ETIM 8.0	EC003628	ETIM 9.0	EC003628
ETIM 10.0	EC003628	ECLASS 14.0	19-17-03-03
ECLASS 15.0	19-17-03-03		

IE-SFP-1FE-SM-30

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Accessories

www.weidmueller.com

LC-Duplex



Mounting rail outlet, LC duplex junction design according to IEC 61754-20

General ordering data

Type	IE-TO-LCD-SM	Version	
Order No.	8947020000	Mounting rail outlet, fibre-optic, LC Duplex, Singlemode, IP20	
GTIN (EAN)	4032248735037		
Qty.	10 ST		