

VPU ZPA I 3 300/7,5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Lightning arresters for 40 mm rail systems

- Simple and safe to use and install
- Complete and permanent status control
- Leakage current free surge protection
- Application-specific application classes with 7.5 kA and 12.5 kA discharge current

General ordering data

Version	Surge voltage arrester, Low voltage, Leakage-current-free, TN-C
Order No.	2674420000
Type	VPU ZPA I 3 300/7,5
GTIN (EAN)	4050118686784
Qty.	1 items
Delivery status	Discontinued
Available until	2023-10-31T00:00:00+01:00
Alternative product	VPU ZPA S I 3 300/7,5

VPU ZPA I 3 300/7,5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Dimensions and weights

Depth	99 mm	Depth (inches)	3.8976 inch
Height	229 mm	Height (inches)	9.0157 inch
Width	47 mm	Width (inches)	1.8504 inch
Net weight	100 g		

Temperatures

Storage temperature	-40 °C...70 °C	Operating temperature	-40 °C...70 °C
Humidity	5...95 %, no condensation		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Optical function display	green = OK; red = arrester is defective - replace	Segment	Power distribution
Version	Leakage-current-free	Design	for 40mm busbars
UL 94 flammability rating	V-0	Colour	grey
Suitable for	Count-in installation (leakage current free)	Protection degree	IP30, in combination with the cover
Operating altitude	≤ 4000 m		

Rated data IEC / EN

Number of poles	3	Leakage current at Un	20 µA
Signalling contact	No	Rated voltage (AC)	240 V
Low voltage network	TN-C	Voltage type	AC
Temporary surge voltage (over-voltage) - TOV	442 V	Fuse protection	No Fuse necessary ≤315 A gG
Response time / fallback time	≤ 100 ns	Suitable for	Count-in installation (leakage current free)
Standards	IEC61643-11, EN61643-11	Lightning test current Iimp (10/350 µs) (L-PE)	7.5 kA
Requirements class, acc. to EN 61643-11	T1, T2	Requirements category acc. to IEC 61643-11	Type I, Type II
Max. continuous voltage, Uc (AC)	300 V	Mains voltage	230 V / 400 V
Energy coordination (≤10 m)	Type I, Type II, Type III	Discharge current In (8/20µs) wire-PE	20 kA
Discharge current I _{max} (8/20µs) wire-PE	50 kA	SPD type	T1, T2
Protection level Up at IN (L/N-PE)	≤ 1.5 kV	Short-circuit current rating ISCCR	25 kA
Follow-on current extinguishing capability Ifi	Follow current need not be taken into account	Integrated back-up fuse	No

VPU ZPA I 3 300/7,5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Connection data

Wire connection method	Screw connection	Type of connection	Clamped
Tightening torque, max.	4.5 Nm	Clamping range, min.	16 mm ²
Clamping range, max.	35 mm ²	Conductor cross-section, flexible, AEH (DIN 46228-1), min.	16 mm ²
Conductor cross-section, flexible, AEH (DIN 46228-1), max.	25 mm ²	Connection cross-section, stranded, min.	16 mm ²
Connection cross-section, stranded, max.	35 mm ²		

Electrical data

Voltage type	AC
--------------	----

General data

Number of poles	3	Protection degree	IP30, in combination with the cover
Colour	grey		


Guarantee

Time interval	5 years
---------------	---------


Classifications

ETIM 8.0	EC001457	ETIM 9.0	EC001457
ETIM 10.0	EC001457	ECLASS 14.0	27-17-12-04
ECLASS 15.0	27-17-12-04		

Drawings



Prinzipschaltbild



VPU ZPA I 3 300/7,5**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germanywww.weidmueller.com**Accessories****Crosshead screwdriver Phillips**

VDE insulated crosshead screwdriver, for Phillips screws, SDIK PH DIN 7438, ISO 8764/2-PH, output to ISO 8764-PH, SoftFinish grip

General ordering data

Type	SDIK PH1 X 80	Version
Order No.	2749890000	Screwdriver, Blade width (B): 1 mm, 80 mm, Blade thickness (A): 1
GTIN (EAN)	4050118897098	
Qty.	1 ST	

Slotted screwdriver

VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

General ordering data

Type	SDIS 1.0X5.5X125	Version
Order No.	2749850000	Screwdriver, Blade width (B): 5.5 mm, Blade length: 125 mm, Blade
GTIN (EAN)	4050118897050	thickness (A): 1 mm
Qty.	1 ST	