


**AAP11 6 LO DL OR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The unique modular concept can be tailored to every type of machine. The potential distribution terminal blocks AAP are successful thanks to their uniform design with two possible constructions – alternating or grouped. In the grouped structure of the control voltage distribution, the potentials are located on different terminal blocks and thus form entire potential blocks.

**General ordering data**

|            |   |
|------------|---|
| Version    | Supply terminal, PUSH IN, 6 mm <sup>2</sup> , 500 V, 41 A, dark beige |
| Order No.  | <a href="#">2675310000</a>  |
| Type       | AAP11 6 LO DL OR  |
| GTIN (EAN) | 4050118733679   |
| Qty.       | 20 items  |

## AAP11 6 LO DL OR

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

|                          |             |                |             |
|--------------------------|-------------|----------------|-------------|
| Depth                    | 48 mm       | Depth (inches) | 1.8898 inch |
| Depth including DIN rail | 48 mm       | Height         | 85.5 mm     |
| Height (inches)          | 3.3661 inch | Width          | 8.1 mm      |
| Width (inches)           | 0.3189 inch | Net weight     | 15.11 g     |

### Temperatures

|                                  |                |                                  |               |
|----------------------------------|----------------|----------------------------------|---------------|
| Storage temperature              | -25 °C...55 °C | Ambient temperature              | -5 °C...40 °C |
| Continuous operating temp., min. | -60 °C         | Continuous operating temp., max. | 130 °C        |

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### Material data

|                                |        |                           |            |
|--------------------------------|--------|---------------------------|------------|
| Basic material                 | Wemid  | Colour                    | dark beige |
| Colour of operational elements | orange | UL 94 flammability rating | V-0        |

### Rating data IECEX/ATEX

|                                |                   |                                 |                   |
|--------------------------------|-------------------|---------------------------------|-------------------|
| Certificate No. (ATEX)         | TUEV17ATEX8030U   | Certificate No. (IECEX)         | IECEXTUR17.0015U  |
| Max. voltage (ATEX)            | 550 V             | Current (ATEX)                  | 33 A              |
| Wire cross section max. (ATEX) | 6 mm <sup>2</sup> | Max. voltage (IECEX)            | 550 V             |
| Current (IECEX)                | 33 A              | Wire cross section max. (IECEX) | 6 mm <sup>2</sup> |
| Marking EN 60079-7             | Ex ec II C Gc     | Ex 2014/34/EU label             | II 2 G D          |

### System specifications

|                               |     |                                     |       |
|-------------------------------|-----|-------------------------------------|-------|
| End cover plate required      | Yes | Number of potentials                | 1     |
| Number of levels              | 1   | Number of clamping points per level | 1     |
| Number of potentials per tier | 1   | Levels cross-connected internally   | No    |
| PE connection                 | No  | Mounting rail                       | TS 35 |
| PE function                   | No  |                                     |       |

### Additional technical data

|                          |       |                  |       |
|--------------------------|-------|------------------|-------|
| Open sides               | right | Snap-on          | Yes   |
| Explosion-tested version | Yes   | Type of mounting | TS 35 |

### Conductors for clamping (additional connection)

Connection type, additional connection PUSH IN

## AAP11 6 LO DL OR

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Conductors for clamping (rated connection)

|   |  |             |                      |       |
|---|--|-------------|----------------------|-------|
| Gauge to IEC 60947-1  | A5                                     |             |                      |       |
| Wire connection cross section AWG, max.   | AWG 8                                  |             |                      |       |
| Connection direction  | top                                    |             |                      |       |
| Stripping length  | 12 mm                                  |             |                      |       |
| Type of connection 2  | PUSH IN                                |             |                      |       |
| Type of connection  | PUSH IN                                |             |                      |       |
| Number of connections   | 1                                      |             |                      |       |
| Clamping range, max.  | 6 mm <sup>2</sup>                      |             |                      |       |
| Clamping range, min.  | 0.34 mm <sup>2</sup>                   |             |                      |       |
| Blade size  | 1.0 x 5.5 mm                           |             |                      |       |
| Wire connection cross section AWG, min.   | AWG 22                                 |             |                      |       |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 6 mm <sup>2</sup>                      |             |                      |       |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.34 mm <sup>2</sup>                   |             |                      |       |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 6 mm <sup>2</sup>                      |             |                      |       |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.34 mm <sup>2</sup>                   |             |                      |       |
| Wire connection cross section, finely stranded, max.                                    | 6 mm <sup>2</sup>                      |             |                      |       |
| Wire connection cross section, finely stranded, min.                                    | 0.34 mm <sup>2</sup>                   |             |                      |       |
| Connection cross-section, stranded, max.  | 6 mm <sup>2</sup>                      |             |                      |       |
| Connection cross-section, stranded, min.  | 0.34 mm <sup>2</sup>                   |             |                      |       |
| Twin wire-end ferrules, max.  | 1.5 mm <sup>2</sup>                    |             |                      |       |
| Twin wire-end ferrules, min.  | 0.5 mm <sup>2</sup>                    |             |                      |       |
| Wire connection cross-section, solid core, max.   | 6 mm <sup>2</sup>                      |             |                      |       |
| Wire connection cross-section, solid core, min.   | 0.34 mm <sup>2</sup>                   |             |                      |       |
| Tube length for wire-end ferrule with plastic collar DIN 46228/4                        | Tube length                            | min.        | 10 mm                |       |
|   |  | max.        | 12 mm                |       |
|   | Cross-section for conductor connection | min.        | 0.5 mm <sup>2</sup>  |       |
|   |  | max.        | 1 mm <sup>2</sup>    |       |
|   | Tube length                            | min.        | 10 mm                |       |
|   |  | max.        | 18 mm                |       |
|   | Cross-section for conductor connection | nominal     | 1.5 mm <sup>2</sup>  |       |
|   | Tube length                            | min.        | 12 mm                |       |
|   |  | max.        | 18 mm                |       |
|   | Cross-section for conductor connection | nominal     | 2.5 mm <sup>2</sup>  |       |
|   | Tube length                            | min.        | 10 mm                |       |
|   |  | max.        | 18 mm                |       |
|   | Cross-section for conductor connection | min.        | 4 mm <sup>2</sup>    |       |
|   |  | max.        | 6 mm <sup>2</sup>    |       |
|   | Tube length for twin wire-end ferrule  | Tube length | min.                 | 10 mm |
|   |  |             | max.                 | 12 mm |
| Cross-section for conductor connection  |  | nominal     | 0.5 mm <sup>2</sup>  |       |
| Tube length   |  | min.        | 10 mm                |       |
|   |  | max.        | 18 mm                |       |
| Cross-section for conductor connection  |  | nominal     | 0.75 mm <sup>2</sup> |       |

**AAP11 6 LO DL OR**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

|   |  |                    |                     |
|---|--|--------------------|---------------------|
| Tube length for wire-end ferrule without plastic collar DIN 46228/1 | Tube length                            | min.               | 12 mm               |
|   |  | max.               | 18 mm               |
|   | Cross-section for conductor connection | min.               | 1 mm <sup>2</sup>   |
|   |  | max.               | 1.5 mm <sup>2</sup> |
|   | Tube length                            | nominal            | 10 mm               |
|   | Cross-section for conductor connection | min.               | 0.5 mm <sup>2</sup> |
|   |  | max.               | 1 mm <sup>2</sup>   |
|   | Tube length                            | min.               | 10 mm               |
|   | Cross-section for conductor connection | min.               | 1.5 mm <sup>2</sup> |
|   |  | max.               | 2.5 mm <sup>2</sup> |
|   | Tube length                            | min.               | 12 mm               |
|   |  | max.               | 18 mm               |
| Cross-section for conductor connection                              | nominal                                | 4 mm <sup>2</sup>  |                     |
| Tube length   | min.                                   | 10 mm              |                     |
|   | max.                                   | 18 mm              |                     |
| Cross-section for conductor connection                              | min.                                   | 6 mm <sup>2</sup>  |                     |
|   | max.                                   | 10 mm <sup>2</sup> |                     |

**General**

|   |        |   |                                  |
|---|--------|---|----------------------------------|
| Number of poles                         | 1      | Wire connection cross section AWG, max. | AWG 8                            |
| Wire connection cross section AWG, min. | AWG 22 | Standards                               | In accordance with IEC 60947-7-1 |
| Mounting rail                           | TS 35  |   |                                  |

**Rating data**

|                                 |                                  |  |         |
|---------------------------------|----------------------------------|--|---------|
| Rated cross-section             | 6 mm <sup>2</sup>                | Rated voltage                                | 500 V   |
| Rated AC voltage                | 500 V                            | Rated DC voltage                             | 500 V   |
| Nominal current                 | 41 A                             | Current at maximum wires                     | 41 A    |
| Standards                       | In accordance with IEC 60947-7-1 | Volume resistance according to IEC 60947-7-x | 0.78 mΩ |
| Rated impulse withstand voltage | 6 kV                             | Power loss in accordance with IEC 60947-7-x  | 1.31 W  |
| Surge voltage category          | III                              | Pollution severity                           | 3       |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000897    | ETIM 9.0    | EC000897    |
| ETIM 10.0   | EC000897    | ECLASS 14.0 | 27-25-01-19 |
| ECLASS 15.0 | 27-25-01-19 |             |             |

Drawings

